

BarcoReality 6500



- High light transmission efficiency thanks to the use of panels with Micro Lens Arrays (MLA).
- Light output of 4,300 ANSI lumens!
- Features three 1,8" polysilicon LCD panels.
- Includes a powerful metal-halide lamp!
- Ideal performance for data images thanks to state-of-the-art optics!
- High quality lenses deliver razor sharp images in every corner and provide superior images without geometric distortion.
- Images with astonishing realism and vibrant colors thanks to Barco's patented TCRPlus Processing Software (True Color Reproduction).
- Resolution: high-quality S-XGA panels
- Thanks to Barco's patented Pixel Map Processor, the projector optimizes the resolution of the incoming sources automatically to map the resolution of the LCD panels.
Result:
crisp graphics with smooth and exceptionally readable characters

- Thanks to Barco's patented Pixel Map Processor, the projector optimizes the resolution of the incoming sources automatically to map the resolution of the LCD panels. Result: crisp graphics with smooth and exceptionally readable characters at all times.
- Need higher light output? Need redundancy for critical presentations? Projector stacking can be done without frames. The motorized lens shift makes projection from an indirect angle possible.
- Projector automatically recognizes the incoming source and optimizes all display settings thanks to AutoImage feature.
- The Projectors offer a light output of 4,300 ANSI lumens, but a noise level below 39 dB(A), thanks to the low noise design! No unwanted distraction for the audience - a common complaint with conventional projectors.
- Easy-to-use remote controls. Backlit infrared remote control with 5 Quick Access Keys for instant access to features like motorized zoom and focus, lens shift, contrast and brightness. Exclusive "executive" remote control available with built-in mouse control and integrated laser pointer will easily direct the audience's attention to a certain part of the screen.
- Digital keystone correction.
- Connect your projector to the corporate network thanks to 10-base T interface, reducing the cost of ownership and resulting in an improved & faster maintenance service
- Connect any PC, notebook, (HD)TV, VCR, DVD, digital video, digital camera or camcorder thanks to the wide array of input connections: Video, S-Video, RGB, VGA, RS232 and Audio.
- Ready to connect future digital sources thanks to optional SDI and FireWire connections.
- Automatic recognition of sources and intelligent user-adjustable priority switching.
- Compatible with all analog & digital sources with resolutions of up to 2000 x 1280 pixels.
- For double or triple stacking applications and easy monitoring, an active SDI & SDO loop-through is provided.
- Thanks to the optional Ethernet 10-base T interface, the projector becomes an IP addressable device and can be connected to the company network. Reduce the total cost of ownership: control and monitor all functions of the projector (brightness, contrast, keystone correction and on/standby) from any networked location, the maintenance office or even remotely receive information about the status of different projectors via email (warnings in power supplies, as well as lamp life, run time and software version) easy software upgrades via the corporate network all of these features result in an improved and faster maintenance service. Example:

- Thanks to the optional Ethernet 10-base T interface, the projector becomes an IP addressable device and can be connected to the company network. Reduce the total cost of ownership:
 - control and monitor all functions of the projector (brightness, contrast, keystone correction and on/standby) from any networked location, the maintenance office or even remotely
 - receive information about the status of different projectors via email (warnings in power supplies, as well as lamp life, run time and software version)
 - easy software upgrades via the corporate networkall of these features result in an improved and faster maintenance service. Example:
"Lamp warning" email will keep you up-to-date on the status of the lamp life for all your projectors at your company site.
- Barco offers 7 easy-to-replace lenses, allowing projection from practically any position and throw distance, without losing brightness .
Choice between fixed focal or zoom lenses going from 0.8 up to 7 times the screen width.
- Easy table or ceiling mount, choose front or rear projection.
Thanks to the motorized lens shift, on-site adjustments are easy, the projector can be placed off-axis up to 112% horizontally and 120% vertically.
- Solid & reliable projector thanks to rugged, die-cast aluminium cabinet.
- Wide range of connectivity:
ready to attach current & future digital sources with SDI and FireWire[®] connections.
- Mature projection platform.
Barco continues to develop and invest in this successful range of projectors.

기술 사양

BARCOREALITY 6500

일반 사양

광 출력	4,300 ANSI lumens
LCD 패널	3 active matrix 1.8" diagonal S-XGA polysilicon LCD panels with Micro Lens Arrays and a resolution of 1280x1024 pixels (5:4 aspect ratio)
밝기 균일도	Brightness uniformity: >80% for the total screen
해상도	1280 x 1024 (native)
전력 소비	900 Watt
호환성	<ul style="list-style-type: none">· All current video sources (PAL, SECAM, NTSC 3.58, NTSC 4.43) in Composite, S-VHS, Component or RGB formats· All currently proposed HDTV, extended and improved television standards (1080i, 720p)· All computer graphics formats from VGA, S-VGA, XGA, S-XGA and U-XGA· Most Macintosh computers· Electronic Workstations with a resolution up to 2000x1280 pixels/76 Hz· Most sources with a pixel clock up to 200 MHz
명암비	> 350:1 (full white/full black) > 180:1 (5x4 checkerboard)
크기(WxLxH)	550 x 710 x 470 mm (21.7 x 28.0 x 18.5 inch)
램프	A new 600 Watt metal-halide arc lamp pre-aligned for maximum light output
렌즈범위	QFD Lenses Motorized V shift: up to 120% Motorized H shift: up to 112% For specific details per lens type: see lens product pages
네트워크 연결	Optional
스크린 크기	1-6 m, except for the QGD (0.8:1) lenses
무이음경계선(Seamless) 전환	Not available
무게	Body only: 17.7 kg/39.0 lbs. Body + lens: 21-25 kg/46.3-55.1 lbs.

작성일: 09 Jul 2024

© 2024 Barco nv. All rights reserved. 서면 허가 없이 전체 또는 부분을 복제하는 것은 금지됩니다. 모든 브랜드명 및 제품명은 상표, 등록 상표 또는 해당 소유자의 상표입니다. 지속적인 혁신으로 인해 정보 및 기술 사양은 사전 고지 없이 변경될 수 있습니다. 최신 사양은 www.barco.com을(를) 확인하세요.