

# eGFX Home Read Station

Flexible remote radiology reading solution



- **Preinstalled MXRT-6700 display controller**
- **4x DisplayPort 1.4 video outputs**
- **2x USB 3.0 ports on the front for added connectivity**
- **RJ 45 Gigabit Ethernet for high speed network connectivity**
- **Dual Thunderbolt™ 3 controllers for dedicated bandwidth**
- **Aluminum design for lightweight performance**
- **Compact design and small footprint**

As a radiologist, with the eGFX Home Read Station you're all set to start reading at home. It's a flexible and mobile radiology workstation solution that assures dependable image quality and consistent workflow wherever and whenever you are working. Using an eGFX station connected over Thunderbolt™ 3, you can enjoy the same imaging performance, workflow productivity and tools at home as in the hospital.

Compatible with Barco displays systems and validated mobile workstations, you'll lose no time and effort in configuring and supporting remote reading stations. With QAWeb Enterprise, quality and compliance of all workstations can be managed remotely, so software updates and security scans can be executed easily.

Remote reading allows radiologists to work more efficiently, ensures optimal working conditions and enables a flexible work schedule. On-call, weekend and late-evening duties, for example, can be performed at home instead of at the hospital. With the millennial generation and digital natives entering the workforce, home reading is becoming a standard benefit in radiology hiring.

Please consult your Barco representative or distributor in your country or territory to confirm availability. A reference to any product or service on this site does not imply that such product is or will be available in your location.

**Product specifications****EGFX HOME READ STATION**

General specifications	
Power consumption	240 W
Operating system	Windows 10 (64-bit)
Platforms	Intel® and AMD architectures
Power Connector	None
Graphics accelerator	AMD Radeon Pro™
Display memory	8GB DDR5
Memory interface	256-bit
Memory bandwidth	160 GB/s
Pixel depth	32-bit pixels (10-bit grayscale and 30-bit color)
Electrical standard	DisplayPort (DP) v1.4
Direct3D hardware support	Microsoft® DirectX v12, Vulkan® 1.1, Shader Model 5.1
OpenGL hardware support	OpenGL 4.5
Connectors	(4x) DisplayPort 1.4
Operational temperature	0° to 55°C
Connectivity	DisplayPort to Single-link DVI adapter available separately 2x USB 3.0 ports on the front for added connectivity RJ 45 ethernet Gigabit LAN connection for high speed network connectivity, located on the back side of the enclosure
Bandwidth	Up to 40Gbps
Cooling	Perforated design and internal fans allow for ample cooling of the graphics card
Cover	Aluminum design for lightweight performance
Dimensions	8.5" x 6" x 2.75"

Last updated: 18 Mar 2024

© 2018 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check [www.barco.com](http://www.barco.com) for the latest specifications.