

OpSpace OpS-110

Small form factor thin client for HD displays



Barco's OPS-110 thin client is a small form factor display controller specifically built to drive up to two displays in HD resolution (1920 x 1080). It is used in Barco OpSpace networked visualization and collaboration environments to display encoded streams coming from an IP network. It supports standard H.264, Barco's low-latency Video2Data (V2D), Virtual Network Computing (VNC) and Remote Display Protocol (RDP) decoding.

Low noise thin client for up to two displays

The OPS-110 is designed and fully qualified for Barco OpSpace environments. Once connected to an OpSpace server, the pre-configured appliance enables customers to capture networked source information from anywhere. It displays these sources with a user-friendly user interface.

Multiple appliances can be combined to show sources as part of a composed desktop on monitors of an OpSpace workstation, a truly unified workspace for mission-critical applications.

This thin client can process up to eight HD-quality sources and allows organizing visual and interactive content as a smart multi-viewer to enhance knowledge and improve decision-making.

Features

- Pre-configured thin client for Barco OpSpace systems
- Linux based OpSpace operating system
- Intel® i7 Quad Core™ processor for low-latency application processing and software based media decoding

- Drives up to two displays in HD resolution (1920 x 1080)
- Processes up to eight HD sources
- Universal IP streaming video decoding (H.264, V2D, VNC, RDP)
- Silent operation
- Small form factor
- Flexible mounting options

Product specifications**OPSPACE OPS-110**

General specifications		
Platforms	OpS-110	
Memory	8 GB RAM	
Network	2x 1Gb/s LAN	
Processor	Intel(R) Core(TM) i7 Quad core CPU 3.4GHz	
Hard disk	128 GB SSD	
Graphics card	Intel HD Graphics 630	
Output	Up to 2x displays HD 1920x1200 @60Hz via DisplayPort (HDMI via included adapters)	
Input	IP video sources (H.264), Video2Data (Barco V2D), Virtual Network Computing (VNC), Remote Desktop Protocol (RDP)	
Form factor		
Dimensions	60 x 190 x 190 mm 2.36 x 7.48 x 7.48 in Packed: 230 x 260 x 308 mm 9.06 x 10.24 x 12.13 in	
Power supply	External PSU 150W / 90 – 264 VAC / 47 – 63 Hz	
Power consumption	Typ. 83W max. 110W	
Weight	2.2kg 4.85 lbs Packed: 4.5kg 9.92 lbs	
Temperature range	0° -40° C 32° -104° F	
Humidity	Max. 80% (non-condensing)	
Noise Level	Max. 32dBa (measured at 1m/32.8ft distance at 22°C/72°F)	
Compliance	CE, CB, UL, RCM, BIS, CU-EAC, FCC Class A CCC contact Barco Sales	
MTBF	50,000 h	
Mounting	Order no.	
	R9811098	P110 VESA Mount (for 1x OPS-110 + 1x PSU)
	R9811099	P110 Rack Mount (for 2x OPS-110 + 2x PSU)

Last updated: 12 Apr 2024

© 2018 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check www.barco.com for the latest specifications.