

# DP2K-32B

Bright DLP Barco Alchemy Cinema projector (33,000 lumens)



- Bright images, low operating cost
- Integrated, DCI-compliant projector
- Combines media server functionalities with Series 3 cinema processing electronics

**Product specifications****DP2K-32B**

<b>General specifications</b>	
Digital MicroMirror Device™	3 x 1.2" DC2K dark metal devices
Native resolution	2,048 x 1,080 pixels
Housing	Hermetically sealed DMDs and optical assembly
Lamp	3kW -7kW (Xenon lamp)
Light output	33,000 lumens (6.5kW lamp factory installed) (more than 34,000 lumens using 7kW lamp)
Screen size	Up to 32m / 105 ft wide
Contrast ratio	2,000:1
Control I/O	3x Ethernet 8x GPIO (DB 25) 3D interface USB RS-232 interface (DB9)
Integrated Cinema Media Processor	DCI 4K 2D up to 60fps DCI 4K 3D (24 or 30 fps per eye) DCI High Frame Rates 2K 3D up to 120fps (60fps per eye) JPEG 2000 bit-rates up to 625Mbps Dual-channel color-correction MPEG-2 (4:2:0 and 4:2:2 up to 60fps) 2x HDMI2.0a (up to 4K 2D 60fps) 2x 3G-SDI inputs 16x AES/EBU audio channels (2x RJ45) 8x GPI, 8x GPO (4x RJ45) 2x Gbe for content connectivity & ingest 2x front-accessible USB 3.0 for fast ingest 2x front-accessible USB 2.0 Video watermarking: Civolution NexGuard Audio watermarking: Civolution Closed captioning devices: Support for SMPTE 430-10
Integrated storage	1.9TB effective storage (RAID-5) / 3x 1TB Hot-swappable 2.5" hard-drives 3.9TB effective storage (RAID-5) / 3x 2TB Hot-swappable 2.5" hard-drives
Barco Web Commander	Projector Dashboard Projector Control Board Show Player/Editor/Scheduler Automation, 3D, Ingest Dynamic DCP playlists & intermission TMS integration Smart Projector Status Via HTML5 web-browsers including iOS & Android tablets Dual projector 3D: passive and active Auro 11.1 decoding
Barco Communicator	Projector installation & configuration Projector update & maintenance
Projector diagnostics	via Integrated Media Server via Communicator control software via SNMP agent
Power requirements	3x 400V + N or 3x 220V 30,000 BTU/hr (with 6.5kW lamp)
Dimensions	604(H) x 754(W) x 1129(D) mm 23.78(H) x 29.69(W) x 44.45(D) inch NB.: min. 5 cm of air inlet spacing required at the bottom of projector
Weight	140 kg (309 lbs)
Ambient temperature	35°C / 95°F Max.
Exhaust airflow	350 – 390 cfm (10 – 11 m <sup>3</sup> /min)
Options	3D add-ons Touch screen monitor, inc. Barco Commander & Communicator Pedestal CineCare Web Auro 11.1 license Barco Escape license Live 3D*** *** Software roadmap
Safety requirements	Class 1 risk group 3

Last updated: 17 May 2023

© 2018 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check [www.barco.com](http://www.barco.com) for the latest specifications.