

# SP4K-55B

52,000 lumens smart cinema projector



- **Brilliant image**
- **Ready for tomorrow, today**
- **Barco EcoPure™**
- **Fit and forget**

SP4K-55B is part of the Series 4 portfolio, designed in close collaboration with industry partners. Market trends in content creation, exhibition and technology were taken into account. The result? A next-generation laser projection family for all cinema screens. The SP4K models come in many different configurations offering you the freedom of choice. A wide range of brightness options, compatibility with both Barco lenses and selected 3rd party lenses, as well as a touch display and live streaming option. Play with the available options to match your specific needs.

## **Brilliant image**

The SP4K models of the Series 4 family brings native 4K resolution, higher contrast and enhanced uniformity into the movie theater. The Barco Active Image Management™ includes patented technology to guarantee sharp, consistent image quality over time.

## **Ready for tomorrow, today**

With the SP4K models and their RGB laser lightsource, the Barco Colorgenic™ technology opens up more than 98.5% of Rec. 2020. Moreover, all SP4K models are fully enabled for future innovations like 4K 120fps and compatibility with the latest immersive audio standard.

## **Fit and forget**

The modular design of the Series 4 projectors allows for cost-effective maintenance. There are only six Barco laser plate™ spare parts to service all light source configurations. Anyone can replace the filters thanks to the toolless cover and filter handling. The SP4K-55B seamlessly integrates into your current setup.

**Product specificaties****SP4K-55B**

General specifications	
Native helderheid	52,000 lumens (typical)
Native contrastverhouding	2000:1 (typical)
Digital MicroMirror Device™	3x 1.38" DC4K
Resolutie	native 4K: 4096 x 2160
Kleurenspectrum	DCI P3 compliant (100% of Rec.2020; when measured in xy-color coordinates)
Lichtbron	Laser
Primelenzen	0.8; 1.01; 1.13-1.72; 1.35-1.86; 1.46-2.10; 1.65-2.60; 2.00-3.35; 2.53-4.98  High-brightness and high-contrast B-lenses compatible
Langdurige stabiliteit van helderheid	40,000 hrs @ average usage conditions
Behuizing	integrated and external cooling design and patented sealed optical assembly
Afmetingen (B x L x H)	projector incl. feet  760 x 1470 x 612 mm  29,92 x 57,54 x 24,09 inches  external cooler: /p> 546 x 462 x 589 mm  21,50 x 18,19 x 23,19 inches
Gewicht	projector incl.feet: 175kg/385lbs  external cooler incl. feet: 31kg/68lbs
Voedingsvereisten	Single phase or triple phase 200-240V 25A  Cooler: obtains power from the projector
Warmtebelasting (max. vermogen)	14,500 BTU/hr
Luchtuitstroom	Projector: 615CFM  External cooler: 450CFM
Omgevingstemperatuur	40°C / 104F max.
Omgevingsvochtigheid	85% RH max.
Mediaserver	Barco Alchemy ICMP-X and other media server brands ** supported
Energieverbruik	4.2kW (3W in Eco mode)
Geluidsniveau	Projector: 51dB(A)  External cooler: details TBC  @1m and 25°C ambient temperature
3D-systemen	Active glasses systems and polarization systems on silver screens are supported. Color separation systems are not supported.
Veiligheidsvereisten	Class 1 risk group 3
Gebruikersinterface	Touch Display and/or web based
Opmerkingen	Cooling liquid hose and cable length: 2.5m or 5m (8.2ft or 16.4ft)  Vertical separation between cooler and projector: Maximum 3m (10ft)  ** projector configuration with ICP-D; contact Barco service for the list of supported brands

Laatst bijgewerkt: 09 Apr 2024

© 2018 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Vanwege voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Raadpleeg [www.barco.com](http://www.barco.com) voor de meest recente specificaties.