

D320



技术规格

D320

一般规格

输入	4 user defined inputs Front accessible Integrated video processing Auto sensing, hot swappable S-video, composite, YUV, RGB SDI, HD-SDI, DVI up to UXGA
兼容性	LED displays
输出	DVI-A, DVI-D, RGB
控制	<ul style="list-style-type: none">· Scaler 4 input channels [Data-Video] fully scalable to desired output resolution· Z-order Instant modification of Z-order control, for each output window· Window positioning Intuitive positioning interface· Connectors RS 232 [RJ11]
效果	Anamorphic imaging Chroma-keying [per input] Alpha-keying [per input] Z-order control Windowing/ View ports
操作T°	0° <-> 45°
电源	240W-480W auto ranging 90-264V (50-60 Hz) Connector: 3 pin IEC
订购信息	R9851570

生成于: 09 Jul 2024

© 2024 巴可公司。保留所有权利。未经书面许可, 禁止全部或部分复制。所有品牌名称和产品名称均为其各自持有者的商标、注册商标或商号。由于不断创新, 信息和技术规格如有变更, 恕不另行通知。请查看www.barco.com.cn以了解最新规格。