

Prime Lens 2.0 - 3.2:1



Product specifications**PRIME LENS 2.0 - 3.2:1**

General specifications

Focus Range	+/-10mm from nominal position.
Shift Range	35% of screen height in all directions.

Last updated: 09 Jul 2024

© 2024 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check www.barco.com for the latest specifications.