

LCS-47

47" native High Definition LCD display with additional HD-SDI inputs



Product specifications**LCS-47****General specifications**

Technology	TFT LCD
Resolution	1920x1080 (full HD)
Lifetime	50,000h average
Colors	16.8 million
Color gamut	76% NTSC
Aspect ratio	16:9
Viewing angle	176°/176°
Response time	6.5 ms
Dots per inch	46 dpi
Color adjustment	3200K, 5400K, 6500K, 9300K, User (R,G,B sliders)
Contrast ratio	1500:1
Brightness	500cd/m ²
Light sensor	Ambient light sensor for automatic dimming
Standard inputs	DVI; VGA (D15); S-Video; Composite Video; Component video (YPbPr, YCbCr) 2 separate inputs with loop through of active inputs HD-SDI – 480i, 576i, 720p, 1080i at 50, 59.94 and 60 Hz
Supported resolution	On composite, S-video and component inputs: PAL-Secam 576i, NTSC 480i On DVI and VGA inputs: VESA: VGA, SVGA, XGA, WXGA, SXGA, SXGA+, UXGA; SMPTE-296M(1280 x 720p); SMPTE-274M (1920 x 1080i and 1920 x 1080p)
Control	-RS232 control (with loop-through); Baud-rate: 115200, 38400, 19200 or 9600 -On Screen Display (OSD) -IR remote control
Audio	Audio pre-amp input module (excl. speakers)
Picture-in-picture	PIP source max. 110 MHz
Input	85V-264V (50Hz-60Hz)
Power consumption	303W
Operating temperature	5° to 40°C (41° to 104°F)
Humidity	Max. 85%
Regulation Compliance	CE, UL, FCC, TÜV, CCC
Cooling	Low noise level 21 dB(A) / fanless cooling
Active screen diagonal	47" (1,194 mm)
Active screen area	1,047.4 x 592.4 mm (41.24" x 23.32")
Dimensions	1,139.4 x 684.4 x 126.2 mm (44.86" x 26.94" x 4.97")
Weight	40.2 kg (88.7 lbs)
Front glass	Optional
Hanging	VESA MIS F, 600, 200, 8 (mounts and table stands are optional)
Warranty	Warranty of the Product is two years. Image retention resulting from prolonged continuous use of the Product is not covered by warranty

Last updated: 09 Jul 2024

© 2024 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check www.barco.com for the latest specifications.