

# SP4K-35B

35,000 lumens smart cinema projector



- **Brilliant image**
- **Ready for tomorrow, today**
- **Barco EcoPure™**
- **Fit and forget**

SP4K-35B is part of the Series 4 portfolio, designed in close collaboration with industry partners. Market trends in content creation, exhibition and technology were taken into account. The result? A 4K RGB projector family, designed for cinema. The SP4K models come in many different configurations offering you the freedom of choice. A range of lumens, compatibility with both Barco lenses and selected 3rd party lenses, and optional touch displays. Play with the available options to match your specific needs.

### Brilliant image

The Series 4 brings native 4K resolution, higher contrast and enhanced uniformity into the movie theater. The Barco Active Image Management™ and its patented precision brightness technology guarantees flawless images with automatic white balances.

### Ready for tomorrow, today

The Barco Colorgenic™ technology opens up the full P3 color space and more than 98.5% of Rec. 2020. SP4K-35B is fully enabled for future innovations like 4K 120fps and HDR images. Deliver stunning results not only on day 1, but consistently throughout the lifetime of the product.

### Barco EcoPure™

This silent running projector (51dB(A)) is fully ready for boothless operation. In addition, the SP4K-35B smartly manages its power consumption resulting in a high projector efficiency of 11.3 lm/W. In eco-mode it consumes even less than 3 Watt. What's more, remote wake up on LAN is possible for scheduled maintenance or ingest.

### Fit and forget

The modular design of the Series 4 projectors allows for cost-effective maintenance. There are only six Barco laser plate™ spare parts to service all light source configurations. Anyone can replace the filters thanks to the toolless cover and filter handling. The SP4K-35B seamlessly integrates into your current setup.

**Product specificaties****SP4K-35B**

General specifications	
Native helderheid	35,000 lumens (typical)
Native contrastverhouding	2000:1 (typical)
Digital MicroMirror Device™	3x 1.38" DC4K
Resolutie	native 4K: 4096 x 2160
Kleurenspectrum	DCI P3 (98.5% of Rec. 2020; when measured in xy-color coordinates)
Lichtbron	Laser
Primelenzen	1.13-172; 1.35-1.86; 1.46-2.10; 1.65-2.60; 2.00-3.35; 2.53-4.98 High-brightness and high-contrast B-lenses compatible
Langdurige stabiliteit van helderheid	40,000 hrs @ average usage conditions
Behuizing	integrated cooling design and patented sealed optical assembly
Afmetingen (B x L x H)	projector incl. feet 760 x 1470 x 612 mm 29,92 x 57,54 x 24,09 inches
Gewicht	163kg/359lbs
Voedingsvereisten	single phase or triple phase 200-240V 20A
Warmtebelasting (max. vermogen)	10,000 BTU/hr
Luchtuitstroom	615CFM
Omgevingstemperatuur	40°C / 104F max.
Omgevingsvochtigheid	85% RH max.
Mediaserver	Barco Alchemy ICMP-X and other media server brands ** supported
Energieverbruik	3.1kW (3W in Eco mode)
Geluidsniveau	51dB(A) @1m and 25°C ambient temperature
3D-systemen	Active glasses systems and polarization systems on silver screens are supported. Color separation systems are not supported.
Veiligheidsvereisten	Class 1 risk group 3
Gebruikersinterface	Touch Display and/or web based
Opmerkingen	** projector configuration with ICP-D; contact Barco service for the list of supported brands

**Laatst bijgewerkt: 28 Feb 2024**

© 2018 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Vanwege voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Raadpleeg [www.barco.com](http://www.barco.com) voor de meest recente specificaties.