

iQ G400



Product specificaties

IQ G400

General specifications

Lichtuitvoer	4,200 ANSI lumen
Helderheidsuniformiteit	Brightness uniformity: >95 % for the total screen
Lcd-panelen	3 active matrix 1.3" diagonal XGA polysilicon LCD panels with Micro Lens Arrays and a resolution of 1024 x 768 pixels (aspect ratio 4:3). LCD panels are selected for a minimum of pixel defects.
Resolutie	1024 x 768 (native)
Lamp	2x 250 Watt UHP lamp, in lamp housing, pre-aligned for max. light output. Typical lifetime: 1000 h/lamp. 1000 hours in Dual Lamp Mode or max. 2000 hours/set in Single Lamp Mode.
Lenzen	Fixed focal length lenses are available with a throw ratio of 0.85:1 (very short throw ratio, specially designed for rear screen on-axis projection) or 7.0:1 (long throw). Variable focus lenses with a throw distance of 1.3-1.8,1.9-2.6,3.0-6.0 times the screen width
Schermafmaat	From 1-6 m/3-20 ft.
Contrastverhouding	>400 : 1 (full white/full black)
Scanfrequenties	Horizontal 15 kHz -110 kHz Vertical 25 Hz -150 Hz
Kenmerken	• Advanced picture-in-picture • Seamless switching with effects • Standard cable basket • Standard light shutter • Advanced digital zoom
Compatibiliteit	The iQ G400 is compatible with: • All current video sources (PAL, SECAM, NTSC) in Composite, S-VHS, Component or RGB formats • All currently proposed HDTV, extended and improved television standards (1080i, 720p) • All computer graphics formats from VGA, SVGA, XGA, SXGA to UXGA • Most Macintosh computers • Electronic workstations with a resolution up to 1600 x 1200 pixels at 75 Hz • Most computer sources with a pixel clock up to 160 MHz • DVI sources up to SXGA
Ingangen	1x Configurable 5-Wire (BNC) for: Composite Video, S-Video, Component Video, RGBHV, RGBS, RGsB. 1x Composite Video (BNC) (up to 7 Composite Video's when using all connectors on top input board) 1x S-Video (4-pin mini-DIN) (up to 3 S-Video's when combining BNC's) 1x VGA (D15 connector) 1x DVI (Digital Visual Interface)
Afmetingen (B x L x H)	Projector body with cable basket: 415 mm (Max W) x 195 mm (Max H) x 565 mm (Max D) Projector body without cable basket: 415 mm (Max W) x 195 mm (Max H) x 487 mm (Max D)
Communicatie	1x D9 connectors for RS232 In/Out 1x spherical IR receiver
Geluidsniveau	
Wisselstroom	Power factor pre-regulated SMPS, 90-254 VAC / 50-60Hz
Energieverbruik	Max 620 Watt
Vermogensdissipatie	Max 2117 BTU/h
Gewicht	Net weight: Body only 12.9 kg / 28.5 lbs. Shipping weight: • without lens max.17.5 kg / 38.5 lbs. • with lens: max.20 kg / 44 lbs.
Lenzverschuiving	QVD Lenses Motorized V shift: -30% +120% For specific details per lens type: see lens product pages
Naadloos schakelen	Standard
Netwerkverbinding	Refer to iQ Pro G400

Laatst bijgewerkt: 09 Jul 2024

© 2024 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Als gevolg van voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Controleer www.barco.com voor de nieuwste specificaties.