

# DP2K-8SLP

Smart Laser cinema projector for screens between 6-9m (20-29 ft)



- **Reduced total cost of ownership**
- **Simple operation**
- **Superior image quality**

The compact SLP projectors are our entry-level laser phosphor projectors for cinema. They're the most cost-effective 2K laser phosphor cinema projectors for smaller movie screens. Driving operational and maintenance costs down, the SLP series offers pristine images and ultimate reliability at a low TCO. As such, they're the perfect choice if you're looking for a worry-free solution to convert your smallest screens to laser with minimal hassle and risk.

### **Reduced total cost of ownership**

Eliminating all lamp-related costs, the DP2K-8SLP provides a very attractive TCO. Thanks to its unique cooling system, the projector boasts a 30,000-hour constant brightness at typical usage conditions. Its significantly higher optical efficiency results in electricity bill savings of up to 40%.

### **Unprecedented ease of mind**

The DP2K-8SLP cuts operating expenses, reduces operational complexity, and optimizes labor cost. The projector increases your uptime and frees you from all lamp-related costs, administration, and maintenance.

### **Superior image quality**

The DP2K-8SLP offers consistent DCI-compliant image quality with 2K resolution, 7,000 lumens brightness, outstanding uniformity and higher contrast on white and silver screens. Its light output can be dimmed to 30% of the initial brightness, enabling 2D and 3D showings from the same projector.

### **Retrofit ready**

If you already own a Barco S-series projector you can replace your current lamp house with the unique laser phosphor retrofit module through an easy on-site upgrade.

**Product specificaties****DP2K-8SLP**

General specifications	
Helderheid	7,000 lumens
Native contrastverhouding	2,000:1
Primelenzen	1.2-1.7; 1.34-1.9; 1.5-2.15; 1.7-2.55; 2.0-3.9
Resolutie	2,048 x 1,080
Langdurige stabiliteit van helderheid	30,000 hrs @ average usage conditions
Afmetingen (B x L x H)	325 x 626 x 925 mm / 12.8 x 24.7 x 36.4 inches
Gewicht	73 kg (161 lb)
Voedingsvereisten	Single phase 200--240V 8A
Warmtebelasting (max. vermogen)	2719 BTU/h
Omgevingstemperatuur	35°C (95°F) Max.
Omgevingsvochtigheid	85% Max.
Energieverbruik	Projector @ full laser power: 1.3 kW
Geluidsniveau	56dB(A)
Mediaserver	Barco Alchemy ICMP and other IMB brands supported.
3D-systemen	Active glasses systems and polarization systems on silver screens are supported. Color separation systems (Dolby3D and 6P) are not supported.
Veiligheidsvereisten	Show safety: the customer shall take precaution for the laser safety (respect the hazard distance and separation height) according to local laser show safety regulations. Workplace safety: the customer shall take precaution for: <ul style="list-style-type: none"><li>▪ workplace safety as prescribed by the local authorities</li><li>▪ basic laser safety training for operators</li><li>▪ laser safety program implementation in the company;</li><li>▪ access limitation only to trained personnel: area labelling, etc.</li></ul>
*	Preliminary specifications

**Laatst bijgewerkt: 17 May 2023**

© 2018 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Vanwege voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Raadpleeg [www.barco.com](http://www.barco.com) voor de meest recente specificaties.