

# BarcoReality 6400



- Extremely high light output of 3400 ANSI lumen
- Three active matrix 1.8" S-XGA Poly-Silicon LCD panels with Micro Lens Array (MLA) and a resolution of 1280 x 1024 pixels
- BARCO's advanced True Color Reproduction feature processes conventional video signals and transforms them into brilliant images with vibrant colors and amazing color depth
- BARCO's patented Pixel Map Processor guarantees very legible characters and the greatest amount of picture detail possible
- Unmatched input compatibility with all analog and digital video sources and all computer graphics formats and electronic workstations up to 2,000 x 1,280 pixels
- Easy picture alignment
- Direct stacking
- Easy lamp and lens replacement
-

- Motorized zoom, focus and lens shift
- Precise projection from any position or distance
- Easy replacement of older generation projectors
- Up to 120 % off-axis projection and extra 25 % keystone correction

技術仕様

BARCOREALITY 6400

一般仕様	
光出力	3400 ANSI Lumen
LCD パネル	3 active matrix 1.8" diagonal S-XGA polysilicon LCD panels with Micro Lens Arrays and a resolution of 1280x1024 pixels (5:4 aspect ratio)
互換性	All Current video sources (PAL, SECAM, NTSC 3.58, NTSC 4.43) in Composite, S-VHS, Component or RGB formats All currently proposed HDTV, extended and improved television standards (Eureka 95, Hi-vision, ACTV, IDTV, EDTV,...) All computer graphics formats from VGA, S-VGA, XGA to S-XGA Most Macintosh computers Electronic Workstations with a resolution up to 2000x1280 pixels/76 Hz Most sources with a pixel clock up to 200 MHz
コントラスト	> 250:1 (full white/full black) > 150:1 (5x4 checkerboard)
ランプ	A new 400 Watt metal-halide arc lamp pre-aligned for maximum light output with a typical lifetime of 1000 hours
対応スクリーンサイズ	From 1-6 m, except for the QGD (0.8:1) lenses
重量	Body only: 17.7 kg/39.0 lbs. Body + lens: 21-25 kg/46.3-55.1 lbs.

生成日:09 Jul 2024

© 2024 Barco nv.(C) Barco. All rights reserved. (無断転載を禁ず。) 書面による許可なく全部または一部を複製することは禁止されています。すべてのブランド名および製品名は、それぞれの所有者の商標、登録商標、または商号です。継続的な技術革新により、情報および技術仕様は予告なく変更される場合があります。最新の仕様についてはwww.barco.comをご確認ください。

