

RetroData 808s + Iris³



技术规格**RETRODATA 808S + IRIS³****一般规格****兼容性**

Horizontal autolock scan frequency of 15-75 kHz
Vertical autolock scan frequency of 37-200 Hz
RGB bandwidth of 75 MHz
A wide range of PC graphics boards with a resolution up to 1280 x 1024 pixels/70 Hz
Universal connection possibilities

光输出

364 ftL. (at 10 % peak white)
41 ftL. (Economy mode)
57 ftL. (Normal mode)
62 ftL. (Boost mode)

屏幕尺寸

67"

生成于: 08 Jul 2024

© 2024 巴可公司。保留所有权利。未经书面许可，禁止全部或部分复制。所有品牌名称和产品名称均为其各自持有者的商标、注册商标或商号。由于不断创新，信息和技术规格如有变更，恕不另行通知。请查看www.barco.com.cn以了解最新规格。