

BarcoReality 909 Split Pack

9" CRT projector designed to meet limited-space requirements for immersive Simulation and V&AR display applications



Технические характеристики BARCOREALITY 909 SPLIT PACK	
Общие характеристики	
Разрешение	12 Line pairs/mm optical >2048 x 1900 ANSI pixels
Объективы	High definition F1.18 hybrid lenses provide large screen razor sharp true color images with outstanding contrast
Светоотдача	• Boost mode: 300 lumens • Normal mode: 250 lumens • Economy mode: 195 lumens 10% full white, 1,250 lumens
Частота сканирования	Horizontal: 30-180 KHz Vertical: 37-240 Hz
Минимальная длительность обратного хода луча	Horizontal: switching point adjustable between 90 and 130 KHz Vertical:
Максимальная адресуемость	3200 x 2560 pixels
Диапазон RGB	180 Mhz
Линейность по горизонтали	< ± 0.25% distortion @ 1280 x 1024, 60 Hz with convergence on green option < ± 1.5% distortion throughout the full horizontal frequency range
Входы	• RGB input on 5 BNC connectors, with automatic sync detection and sync polarity, with sync on green or separate sync • Second RGB analog input on D15-connector, with automatic sync detection and polarity
Потребляемая энергия	Power factor corrected ranging between 100 and 240 VAC +6%/-10%
Энергопотребление	800 W max.

Создано: 09 Jul 2024

© 2024 Барко нв. Все права защищены. Полное или частичное воспроизведение без письменного разрешения запрещено. Все названия брендов и продуктов являются товарными знаками, зарегистрированными товарными знаками или торговыми наименованиями соответствующих владельцев. В связи с непрерывными обновлениями информация и технические характеристики могут меняться без предварительного уведомления. Пожалуйста, проверьте www.barco.com для получения последних спецификаций.

www.barco.com

