

OverView mP50

50" Display Wall system integrating 3-panel Poly-Silicon LCD technology with XGA resolution.



Product specificaties

OVERVIEW MP50

General specifications	
Resolutie	XGA
Kleuren	16.7 millions Color management 30 bit/pixel
Lamp	• 100W lamp • operation time typ. 8000 hours (average) integrated in a pre-adjusted lamp module, no re-adjustment after replacement
Wisselstroom	95-230 VAC ± 10%, 50-60 Hz
Vermogen	140 W
Luminantie	250 cd/m² 73 ftL
Helderheid	600 lumens
Contrast	250:1
Helderheidsuniformiteit	> 95%
Afmetingen structuur	• Diagonal 50" • Width 1,000 mm / 39.37 in. • Height 750 mm / 29.53 in. • Depth 568 mm / 22.36 in. • Weight 45 kg / 99.2 lbs
Naleving van milieuwetgeving	operating temperature 0-40°C 30-105°F humidity max. 80% (non condensing)
Schermen	HVA type 50 " screen Width 1000 mm 39.37 in. Height 750 mm 29.53 in. Depth 96.5mm 2.77 in. Weight 9 kg 19.84 lbs

Laatst bijgewerkt: 09 Jul 2024

© 2024 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Als gevolg van voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Controleer www.barco.com voor de nieuwste specificaties.

