


X2.8R

2.85mm pixel pitch, 1,200 nits true cross-rentable LED display



The X2.8R is a 2.8mm pixel pitch LED display that's designed for the rental and staging market. It brings superior image quality, true cross-rentability features, peace of mind and quick install to live events.

Superior image quality

Thanks to its Infinipix™ processing, the X2.8R provides excellent image quality. Day or night, it offers stunning image quality in both dimmed and high-brightness mode. The display accurately reproduces the colors you have in mind, in all lighting conditions. Infinipix™ processing guarantees smooth video synchronization, without tearing or stutter.

Reliable and easy to set up

If your image fails, your show fails. The X2.8R guarantees peace of mind as the redundant data path automatically takes over in case of failures. The e-mail status notifications allow you to proactively manage your displays. The X2.8R consists of a carbon fiber frame makes it strong and light at the same time.

What's more, it's beam can be both used as a truss or footer so the investment in hardware is limited to the absolute minimum.

If you need to swap an LED module, the Infinipix™ architecture allows this action to be performed in barely minutes...

Truly cross rentable

Thanks to our proprietary calibration technology, the X2.8R is perfectly suited for cross-renting. In this way, you can endlessly combine LED tiles from different rental companies to execute large projects. The X2.8R guarantees consistent brightness and image quality across your entire surface at all times.

Product specificaties

X2.8R

General specifications	
Pixelpitch	2.85 mm / 0.112 inch
Pixeldichtheid	122,500 px/sqm
Pixels per paneel	168 x 168 px (H x V)
Led-type	SMD RGB Black
Helderheid	1,200 nits
Vernieuwingssnelheid	3,840 Hz
Kleurverwerking	16 bit
Kleuren	281 trillion
Verwerking	Infinipix™
Broncompatibiliteit	see Infinipix™
Gegevensverbinding	1G Infinipix(TM)
Hor. kijkhoek	+/-80° (min 50% brightness)
Vert. kijkhoek	+/-80° (min 50% brightness)
Paneelgrootte (B x H x D) in mm	480 x 480 x 89 mm / 18.90 x 18.90 x 3.50 inch
Paneelmateriaal	Carbon
Gewicht / tegel	7kg / 15.4 lbs
Curvecapaciteit	-7.5°/-5°/-2.5°/0°/2.5°/5°/7.5°
Onderhoudsgemak	Front/back
Ingangsspanning	100-240V / 50-60Hz
Energieverbruik	570W/sqm -53W/sqf max. 244 W/sqm -23W/sqf typical
Warmte-dissipatie	1,950 BTU/h/sqm(max) 832 BTU/h/sqm (typical)
Bedrijfstemperatuur	-10° -+40°C / 14° -104°F
Operationele vochtigheid	10-90%
Koeling	Passive cooling
IP-classificatie	Indoor only

Laatst bijgewerkt: 08 Jul 2024

© 2024 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Als gevolg van voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Controleer www.barco.com voor de nieuwste specificaties.

