

X-PORT 3G-SDI



Push-in module easily fitted to the back of the projector Cable lengths up to 300 meters are supported without loss of quality Supports bandwidths up to 2.970 Gbit/s Backward compatible with HD-SDI Active stereo 3D capabilities when combined with X-PORT™ DCC 120 Dual Channel Combiner Available formats for the 3G-SDI module

Format	HDSDI	3G SDI
720 59, 94p	x	x
720 60p	x	x
1,080 23, 98p	x	1,080 23, 98sF
1,080 24sF	x	1,080 24sF
1,080 25p	x	1,080 29, 97p
1,080 30p	x	1,080 30p
1,080 59, 94i	x	1,080 59, 94i
1,080 60i	x	1,080 60i
1,080 59, 94p	x	1,080 59, 94p
1,080 60p	x	1,080 60p

- Push-in module easily fitted to the back of the projector
- Cable lengths up to 300 meters are supported without loss of quality
- Supports bandwidths up to 2.970 Gbit/s
- Backward compatible with HD-SDI
- Active stereo 3D capabilities when combined with X-PORT™ DCC 120 Dual Channel Combiner

1 Requires DCC 120 X-PORT module