



X2.8R

2.85mm pixel pitch, 1,200 nits true cross-rentable LED display



The X2.8R is a 2.8mm pixel pitch LED display that's designed for the rental and staging market. It brings superior image quality, true cross-rentability features, peace of mind and quick install to live events.

Superior image quality

Thanks to its Infinipix™ processing, the X2.8R provides excellent image quality. Day or night, it offers stunning image quality in both dimmed and high-brightness mode. The display accurately reproduces the colors you have in mind, in all lighting conditions. Infinipix™ processing guarantees smooth video synchronization, without tearing or stutter.

Reliable and easy to set up

If your image fails, your show fails. The X2.8R guarantees peace of mind as the redundant data path automatically takes over in case of failures. The e-mail status notifications allow you to proactively manage your displays. The X2.8R consists of a carbon fiber frame makes it strong and light at the same time.

What's more, it's beam can be both used as a truss or footer so the investment in hardware is limited to the absolute minimum.

If you need to swap an LED module, the Infinipix™ architecture allows this action to be performed in barely minutes...

Truly cross rentable

Thanks to our proprietary calibration technology, the X2.8R is perfectly suited for cross-renting. In this way, you can endlessly combine LED tiles from different rental companies to execute large projects. The X2.8R guarantees consistent brightness and image quality across your entire surface at all times.

Product specifications**X2.8R****General specifications**

Pixel pitch	2.85 mm / 0.112 inch
Pixel density	122,500 px/sqm
Pixels per tile	168 x 168 px (H x V)
LED type	SMD RGB Black
Brightness	1,200 nits
Refresh rate	3,840 Hz
Color Processing	16 bit
Colors	281 trillion
Processing	Infinipix™
Source compatibility	see Infinipix™
Data connection	1G Infinipix(TM)
Hor. viewing angle	+/-80° (min 50% brightness)
Vert. viewing angle	+/-80° (min 50% brightness)
Tile size (WxHxD) in mm	480 x 480 x 89 mm / 18.90 x 18.90 x 3.50 inch
Tile material	Carbon
Weight / Tile	7kg / 15.4 lbs
Curve capability	-7.5°/-5°/-2.5°/0°/2.5°/5°/7.5°
Serviceability	Front/back
Input voltage	100-240V / 50-60Hz
Power consumption	570W/sqm -53W/sqf max. 244 W/sqm -23W/sqf typical
Heat dissipation	1,950 BTU/h/sqm(max) 832 BTU/h/sqm (typical)
Operational temperature	-10° -+40°C / 14° -104°F
Operational humidity	10-90%
Cooling	Passive cooling
IP rating	Indoor only

Last updated: 08 Jul 2024

© 2024 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check www.barco.com for the latest specifications.