

DLite 28



Product specifications**DLITE 28****General specifications**

Visual Resolution	28.0 mm
Physical Resolution	28.0 mm
Light output	5.000 Nit (at 6500 °K on a calibrated wall)
Hor. viewing angle	120° (minimum 50% brightness)
Vert. viewing angle	60° (minimum 50% brightness)
Optimal viewing distance	45 meter
Tile dimensions	Width: 0.448 Height: 0.448 Weight: 14 kg
Screen size	Unlimited
Avg Power Consumption	350 Watt/sqm
Max. power consumption	1750 Watt/sqm
Outdoor Compliance	IP 65

Last updated: 10 Jul 2024

© 2024 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check www.barco.com for the latest specifications.