

# BarcoGraphics 808s + Iris<sup>3</sup>

High Performance Graphics Projector



**Product specifications****BARCOGRAPHICS 808S + IRIS<sup>3</sup>**

General specifications	
<b>Compatibility</b>	Display compatibility from VHS Video up to 1600 by 1200 pixel workstations Horizontal autolock scan frequency range of 15-110 kHz Vertical scan frequency of 37-200 Hz autolock RGB bandwidth of 120 MHz Universal connection possibilities
<b>Contrast</b>	>1000:1 (full white/full black)
<b>Light output</b>	1250 Lumen (at 10 % peak white)
<b>Screen size</b>	Min.: 1.4 m x 1.05 m (4.6' x 3.45') Max.: 6.0 m x 4.5 m (20' x 15')

Last updated: 15 Mar 2023

© 2018 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check [www.barco.com](http://www.barco.com) for the latest specifications.