

# Hydra Compact Twin

Universal multi video insertion unit



**Product specifications****HYDRA COMPACT TWIN****General specifications**

Dimensions	<ul style="list-style-type: none"><li>• 19" industrial case, height in rack units: 4U</li><li>• Width case: 440 mm   17.32"</li><li>• Width with fixation: 483 mm   18.98"</li><li>• Depth case: 540 mm   21.30"</li><li>• Depth handles: 50 mm   1.90"</li><li>• Height: 177 mm   6.97"</li></ul>
Heat dissipation	1550 BTU
Inputs	All input units have full decoding, scaling, filtering and scan conversion capabilities on board and perform these tasks independently from the other boards in the system.
Number of slots for in and output boards	2 x 4
Power consumption	450W
Power supply	<ul style="list-style-type: none"><li>• Number of power supplies: 3 (hot-swap, redundant)</li><li>• Number of power leads: 3</li><li>• Power supply: 100-240 VAC, 47-63 Hz</li></ul>
Weight	21 kg

Last updated: 09 Jul 2024

© 2024 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check [www.barco.com](http://www.barco.com) for the latest specifications.