

# QSD(1.2:1) Lens



**Product specifications****QSD(1.2:1) LENS****General specifications**

Distortion	< 1%
EFL	258 mm / 10.16"
Length	135 mm / 5.3"
Max Diameter	135 mm / 5.3"
Net Weight Dimensions	3.0 kg / 7.7 lbs
Projection Distance	1.5 -7.5 m / 57 -296"
Relative Luminance	102%
Resolution	MTF > 65% @ 2.4 lp / mm 6 lp / "
Screen Width (min / max)	1 -6 m / 39 -236"
Throw Ratio	1.2

Last updated: 09 Jul 2024

© 2024 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check [www.barco.com](http://www.barco.com) for the latest specifications.