


# NX-4

<P>4mm pixel pitch, 2,000 nits, true black, surface-mounted LED tile</P><br>



**Product specifications****NX-4****General specifications**

Pixel pitch	4.66 mm
Brightness	2,000 nits
LED configuration	3-in-1 SMD
Pixel density	10,368 LEDs per tile (96x108)
Pixel density	10,368 LEDs per tile (96x108)
Hor. viewing angle	120° (min 50% brightness)
Vert. viewing angle	+48, -55° (min 50% brightness)
Contrast ratio	4,000:1 (at 500 lux)
Lifetime	60,000 hours to 75% of initial brightness
Power consumption	239 W/tile (max) 99 W average
Operation power voltage	200-240V / 50-60Hz
Tile dimensions	Width: 448mm (17.6") Height: 504mm (19.8") Depth: 210mm (8.27")
Tile dimensions	Width: 448mm (17.6") Height: 504mm (19.8") Depth: 210mm (8.27")
Tile dimensions	Width: 448mm (17.6") Height: 504mm (19.8") Depth: 210mm (8.27")
Tile dimensions	Width: 448mm (17.6") Height: 504mm (19.8") Depth: 210mm (8.27")
Weight / Tile	12.9 kg
IP rating	Indoor use only
Processing	16 bit/color
Colors	281 trillion
Refresh rate	3,200Hz
Foot build-up	Max. 12 tiles high
Truss build-up	Max. 15 tiles high
Link interface	NNI interface (HDMI connector)
Max link length	10m (with Barco HDMI cable)
Interfaces	4x HDMI link 1x USB (diagnostic)
Max power cascade connection	8 tiles
Serviceability	Front and back (tools required for front)
Operating temperature	0-40°C
Storage temperature	-20 -60°C
Operational humidity	35-85%
Storage humidity	10-90%
Source compatibility	CVBS, YC, YUV, RGB, DVI (Single and Dual link , up to 2048x1536) SDI, HD-SDI, Dual link HD-SDI
Operable digitizer	DX-700 (with NNI output card)
Certifications	CE class A, TUV, FCC Class A, ETL, Cebec

**Last updated: 08 Jul 2024**

© 2024 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check [www.barco.com](http://www.barco.com) for the latest specifications.