


Ushio 4000W DXL-40BAF/L



For more information contact Barco.

Product specifications**USHIO 4000W DXL-40BAF/L****General specifications**

Supplier	USHIO
Supplier order numbers	DXL-40BAF/L
Warranty hours	1400

Last updated: 15 Mar 2023

© 2018 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check www.barco.com for the latest specifications.