

iQ Pro G200L



Specifiche tecniche

IQ PRO G200L

Specifiche generali

Emissione luminosa	2.000 ANSI lumen
Uniformità della luminosità	>95 % for the total screen
Rapporto di contrasto	>400 : 1 (full white/full black)
Pannelli LCD	3 active matrix 1.3" diagonal XGA polysilicon LCD panels with Micro Lens Arrays and a resolution of 1024 x 768 pixels (aspect ratio 4:3).
Risoluzione	1024 x 768 (native)
Connessione in rete	iQ Pro Server Specifications: -Processing Power: Pentium III socket with 1,2 Gigahertz Tualatin Celeron processor -Memory: 256 MB RAM -Storage: 40 GB hard disk -Video memory: up to 64 MB -Inputs and outputs ■ PCMCIA slot for Wireless LAN cards, memory cards, Bluetooth, input extensions ... ■ RJ45connector for Ethernet (10Mb/s) and Fast Ethernet (100Mb/s) ■ 4 USB connectors ■ Audio: 3,5 mm jacks for Microphone in, Line in and Line out
Caratteristiche	- Advanced picture-in-picture - Seamless switching with effects - Standard cable basket - Standard light shutter - Advanced digital zoom
Compatibilità	The iQ Pro G200L is compatible with: ■ All current video sources (PAL, SECAM, NTSC) in Composite, S-VHS, Component or RGB formats ■ All currently proposed HDTV, extended and improved television standards (1080i, 720p) ■ All computer graphics formats from VGA, SVGA, XGA, SXGA to UXGA ■ Most Macintosh computers ■ Electronic workstations with a resolution up to 1600 x 1200 pixels at 75 Hz ■ Most computer sources with a pixel clock up to 160 MHz ■ DVI sources up to SXGA
Dimensioni schermo	From 1-6 m/3-20 ft.
Ingressi	1x Configurable 5-Wire (BNC) for: Composite Video, S-Video, Component Video, RGBHV, RGBS, RGsB. 1x Composite Video (BNC) (up to 7 Composite Video's when using all connectors on top input board) 1x S-Video (4-pin mini-DIN) (up to 3 S-Video's when combining BNC's) 1x VGA (D15 connector) 1x DVI (Digital Visual Interface)
Lampada	2x 120 Watt UHP lamp, in lamp housing Typical lifetime: 6000 h/lamp. 6000 hours in Dual Lamp Mode or max. 12000 hours/set in Single Lamp Mode.
Ottiche	Fixed focal length lenses are available with a throw ratio of 0.85:1 (very short throw ratio, specially designed for rear screen on-axis projection) or 7.0:1 (long throw). Variable focus lenses with a throw distance of 1.3-1.8, 1.9-2.6, 3.0-6.0 times the screen width
Frequenze di scansione	Horizontal 15 kHz -110 kHz Vertical 25 Hz -150 Hz
Spostamento obiettivo	QVD Lenses Motorized V shift: -30% +120% For specific details per lens type: see lens product pages
Dimensioni (PXLXA)	Projector body with cable basket: 415 mm (Max W) x 195 mm (Max H) x 565 mm (Max D) Projector body without cable basket: 415 mm (Max W) x 195 mm (Max H) x 487 mm (Max D)
Peso	Net weight, body only: 12.9kg/28.5 lbs
Comunicazione	1x D9 connectors for RS232 In/Out 1x spherical IR receiver
Alimentazione CA	Power factor pre-regulated SMPS, 90-254 VAC / 50-60Hz
Livello di rumore	Max 380 Watt
Consumo energetico	Max 1297 BTU/h
Dissipazione alimentazione	Compliant with UL1950 and EN60950
Norme di sicurezza	BARCO's iQ Pro G200L complies with FCC rules & regulations, part 15 Class B and CE EN55022 Class B
Interferenza elettromagnetica	Standard
Commutazione continua	

Generato il: 09 Jul 2024

© 2024 Barco nv. Tutti i diritti riservati. La riproduzione totale o parziale è proibita in assenza di autorizzazione scritta. Tutti i nomi di marchi e di prodotti sono marchi, marchi registrati o nomi commerciali dei rispettivi proprietari. A causa delle continue innovazioni, le informazioni e le specifiche tecniche sono soggette a modifiche senza preavviso. Controlla www.barco.com per le specifiche più recenti.