


FLD 2.37 - 3.79 : 1 (EN14)

2.56 - 4.1 : 1 (SX+) / 2.37 - 3.79 : 1 (WUXGA)



Focus range: 3.0 - 30.0 m

- SX+ 2.56-4.10:1
- 1080 / WUXGA 2.37-3.79:1

Product specifications

FLD 2.37 - 3.79 : 1 (EN14)

General specifications	
Working F/#	F 2.1-2.72 Motorized Iris F# 2.1-6.5
Zoom ratio	1.6 Motorized zoom and focus
Focal length	49.1-78.6 mm
Focus Range	Standard: 3.0m – 30m
Custom focus range	Extended focus range is available, please contact sales for details
Weight	2.5 kg
Throw Ratio	DMD chip <ul style="list-style-type: none">1080p/WUXGA 2.37-3.79:1SXGA+ 2.56-4.1:1720p 2.8-4.49:1XGA 3.5-5.6:1
Image size tolerance +/-5%	

Last updated: 09 Jul 2024

© 2024 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check www.barco.com for the latest specifications.

