


Njord Cinemascope

Njord Cinemascope has a pleasing calm uniform image and is designed for large screens or high ambient light environments.



- Theater & Media Room Series
- 5K UHD Resolution (5,120 x 2,160)
- 3-Chip DLP
- Up to 9,000 ANSI Lumens

Njord Cinemascope inherits everything from Njord except the aspect ratio, Njord Cinemascope's high-capacity 2.37:1 aspect DLP engine. Its exceptional design allows a cinemascope film to be shown without requiring an anamorphic lens. The light source and optical engine are completely redesigned, made smaller, more efficient, and most importantly optimized for perfect cinematic colors compared to the older model Wodan.

Our Njord Cineascope features a pleasing and uniform image with the power light up large cinemascope screens, whilst delivering an unbelievably detailed image with spectacular color fidelity for an unmatched experience that will delight even the most discerning clients.

Single Step Processing SSP™

Pulse is a hardware and software based platform that simplifies the signal allowing it to transmit from source to screen much faster and more efficiently. We use an advanced image processing technique to display the image on the screen without any artefacts and with the lowest possible processing lag (

State of the art electronics

All new Pulse electronics have been designed to process 4K with HDMI™ 2.0a and HDCP 2.2 and the optical engine utilises the very latest 0.9" DMD DLP chipset, delivering 5,120 x 2,160 pixels to screen. Njord CS also features HDR, motorised lenses and Barco's unique RealColor processing, enables simple and accurate calibration to any desired color standard or white point.



Building Blocks

Njord Cinemascope offers 5K UHD resolution (5,120 x 2,160) for superb image quality. Thanks to its modular design of only five building blocks, Njord CS is easy to service. Njord CS is the most compact and rugged cinemascope projector offering 9,000 lumens light output currently available.

Laser Light Source

Outstanding image quality also requires an exceptional light source which is why we designed Njord CS with a brand new laser engine, significantly improving image uniformity (95%) over its predecessor. Njord CS uses custom selected lasers to secure that we can deliver DCI/P3 color gamut.

Lasers last longer than traditional projector lamps, are not as fragile and offer nearly instant on/off.

Specifiche tecniche

NJORD CINEMASCOPE

Specifiche generali

Tipo proiettore	Three chip DLP
Durata della sorgente luminosa	Up to 20,000
CLO (emissione luminosa costante)	Yes
Schermo paralucente ottico	Yes
Tecnologia	3 x 0.90" DMD™ with sealed core
Server web integrato	Yes
Risoluzione	5120 x 2,160 (5K UHD)
Diagnostica	via Prospector web interface
Rapporto di aspetto	2.37:1 (CinemaScope)
Fonte di luce	Laser phosphor
Potenza luminosa	Up to 9,000 ANSI Lumens Dimable to 4,000 lumens NOTE: Up to 6,940 ANSI Lumens @ 110v
Rapporto di contrasto	20,000:1 (with DynaBlack enabled), 2,000:1 Sequential 600:1 ANSI
Uniformità della luminosità	>90%
Risoluzioni di input	HDMI™: Up to 4,096 x 2,160 @ 24/25/30/50/60Hz DisplayPort (Single Input): Up to 4,096 x 2,160 @ 24/30/50/60Hz via Optional Quad DP1.2 Input Card DisplayPort (Layout Mode: 2 x 2) *: Up to 1,920 x 1,080 @ 120Hz Up to 2,048 x 1,080 @ 120Hz DisplayPort (Layout Mode: 4 x 1) *: Up to 960 x 2,160 @ 120Hz * Specialist GFX cards may be required
Gamma delle lenti	(R9801661) -TLD+ (0.41:1) -90 Degree Lens (R9862001) -TLD+ (0.73 -0.94:1) -90 Degree Lens (R9801414) -TLD+ (0.92 -1.33:1) (R9862005) -TLD+ (1.24 -1.56:1) (R9862010) -TLD+ (1.49 -2.02:1) * (R9862020) -TLD+ (2.01 -2.76:1) * (R9862030) -TLD+ (2.69 -4.41:1) * (R9862040) -TLD+ (4.37 -7.35:1) * (R9829997) -TLD+ (6.95 -10.83:1) * Standard Lens Option(s)
Latenza	TBD
Spostamento della lente ottica	Up to 97% shift & up to 28% horizontal lens shift (depending on lens selection) Visit the Barco Residential Lens Calculator for further information Download Lens & Airflow Data Here
Correzione del colore	P7 RealColor™
Gamut di colore	Up to DCI (P3)
Elaborazione delle immagini	Embedded Warp & Blend Engine
WARP	4-Corner Warp & Bow Correction via Warp Engine
Orientamento	360° Rotation
Connessione di rete	10/100 Ethernet via RJ45 connection
Umidità operativa	0 to 80% (relative humidity)
HDR	HDR10
3D	Active Stereoscopic 3D Additional hardware required please contact an authorized Barco representative for details
Ingressi	1 x HDMI™ 2.0 (HDCP 2.2) 2 x HDBaseT (HDCP 1.4 -9Gbps only) 1 x Display Port 1.2 Quad 3G / 12G SDI / BarcoLink 1 x RJ45 Ethernet 1 x RS232 1 x USB 2 x DMX (1 x Input / 1 x Output) 1 x XLR for Wired Remote 2 x 3D Sync (1 x Input / 1 x Output) Optional Upgrade: Quad DP1.2
Controllo	IR, RS232, IP, 12v Trigger Driver modules available for: Crestron, Control4, RTI & Savant WiFi (Optional), XLR Wired Remote, GSM (Optional)
Dimensioni con imballo (P x L x A)	Including Pallet -Excluding Lens (Packaged Separately) 850 x 665 x 613 mm 33.46 x 26.18 x 24.13 in.
Peso con imballo	TBD
Requisiti di alimentazione	110 -130V / 200 -240V / 50 -60Hz
Accessori standard	Power Card / Remote control
Certificazioni	CE, FCC Class A and cCSAus
Consumo energetico	1,723 W Max

Specifiche tecniche**NJORD CINEMASCOPE**

Livello di rumore (tipico a 25°C/77°F)	43 dB(A)
Temperatura di esercizio	0 to 40 °C at Sea Level Optimal Set Point: 20 °C
*	Firmware upgradable Please contact an authorized Barco representative for details
BTU/ora	Max. 5,876 BTU/h @ 200 -240V Max. 4,811 BTU/h @ 110 -130V
Requisiti del flusso d'aria	Air Inlet (from Rear w/Feet Down): Front / Top / Right Exhaust (from Rear w/Feet Down): Rear Clearance Requirements: Front: 40cm Left: 1cm Right: 40cm Rear: 40cm Top: 40cm
Flusso d'aria di scarico	152 ft ³ /min @ 25 °C 258 m ³ /hour @ 25 °C Download Lens & Airflow Data Here
Dimensioni (P x L x A)	Excluding Lens 850 x 665 x 613 mm 33.46 x 26.18 x 24.13 in.
Peso	Excluding Lens 48kg / 105bs
Garanzia	Limited 3 years parts and labor Extendable up to 5 years
Requisiti di sicurezza	This projector may become Risk Group 3 (RG3) when an interchangeable lens with throw ratio greater than 2.3 is installed. Refer to the installation manual for further information.

Generato il: 27 Dec 2024

© 2024 Barco nv. Tutti i diritti riservati. La riproduzione totale o parziale è proibita in assenza di autorizzazione scritta. Tutti i nomi di marchi e di prodotti sono marchi, marchi registrati o nomi commerciali dei rispettivi proprietari. A causa delle continue innovazioni, le informazioni e le specifiche tecniche sono soggette a modifiche senza preavviso. Controlla www.barco.com per le specifiche più recenti.