

OverView mP50

50" Display Wall system integrating 3-panel Poly-Silicon LCD technology with XGA resolution.



技术规格

OVERVIEW MP50

一般规格

分辨率	XGA
颜色	16.7 millions Color management 30 bit/pixel
灯泡	<ul style="list-style-type: none">· 100W lamp· operation time typ. 8000 hours (average) integrated in a pre-adjusted lamp module, no re-adjustment after replacement
电源	95-230 VAC ± 10%, 50-60 Hz
电源	140 W
亮度	250 cd/m ² 73 ftL
亮度	600 lumens
对比度	250:1
亮度均匀性	> 95%
尺寸结构	<ul style="list-style-type: none">· Diagonal 50"· Width 1,000 mm / 39.37 in.· Height 750 mm / 29.53 in.· Depth 568 mm / 22.36 in.· Weight 45 kg / 99.2 lbs
运行环境	operating temperature 0-40°C 30-105°F humidity max. 80% (non condensing)
屏幕	HVA type 50 " screen Width 1000 mm 39.37 in. Height 750 mm 29.53 in. Depth 96.5mm 2.77 in. Weight 9 kg 19.84 lbs

生成于: 09 Jul 2024

© 2024 巴可公司。保留所有权利。未经书面许可，禁止全部或部分复制。所有品牌名称和产品名称均为其各自持有者的商标、注册商标或商号。由于不断创新，信息和技术规格如有变更，恕不另行通知。请查看www.barco.com.cn以了解最新规格。