


Atlas67.C4DLP



기술 사양

ATLAS67.C4DLP

일반 사양	
AC 전원	100-240 VAC, 50-60 Hz, 1.6-0.7A
호환성	Barco's Atlas integrates with the existing network environment and video sources via BARCO's graphical control units: EOS Compact, Power and Ultra, Hydra and Visu+.
명암비	XGA -350:1 (full field contrast)
크기 구조	• Width 1368 mm / 53.86 in. • Height 1026 mm / 40.39 in. • Footprint 753 mm / 29.65 in. • Depth 897 mm / 35.32 in. • Socket height (min) 614 mm / 24.17 in. • Socket height (max) 1288 mm / 50.70 in • Weight 130 kg / 238.1 lbs
환경 규정 준수	• Operating temperature: 17 °C -27 °C or 62 °F -80 °F (stitched screen) 0 °C - 40 °C or 30 °F - 105 °F (screen module) • Humidity: 40% -60%, non condensing (stitched screen) max 80%, non condensing (screen module)
램프	120 Watt UHP™ lamp
휘도	XGA -100 cd/m²
음선	All projector settings are accessible through Barco's wall management software. Full features of this software can be viewed under this website 'Application software'
전력 소비	XGA -160 W
해상도	XGA -1024x768 pixels
스크린 크기	• 67" diagonally • High contrast black type screens for wide viewing angles • Other screens on request

작성일: 08 Jul 2024

© 2024 Barco nv. All rights reserved. 서면 허가 없이 전체 또는 부분을 복제하는 것은 금지됩니다. 모든 브랜드명 및 제품명은 상표, 등록 상표 또는 해당 소유자의 상표입니다. 지속적인 혁신으로 인해 정보 및 기술 사양은 사전 고지 없이 변경될 수 있습니다. 최신 사양은 www.barco.com을(를) 확인하세요.

