

# RLM H5 Performer

With its compact design and sealed optics, the RLM G5 Performer has proven itself to be an ideal all-round projector suitable to both the rental and staging markets.



**Product specificaties****RLM H5 PERFORMER**

General specifications	
Lichtuitvoer	4500 ANSI Lumen
Resolutie	1280 x 720 (native)
Contrastverhouding	1000 : 1 (full field)
Modus voor hoog contrast	Available with special lenses
Helderheidsuniformiteit	> 90%
Lamp	2 x 250 W mercury max. lifetime: 1500 hrs typ. lifetime: 1000 hrs min. lifetime: 750 hrs
Geluidsniveau (bij 20°C -68°F)	42 dBa
Geluidsniveau (bij 40°C -104°F)	46,5 dBa
Omgevingstemperatuur	Max 40°C (104°F)
Energieverbruik	700 W
Netspanning	92-240 V
Gewicht	Projector: 25 kg (56 lbs) Frame: 5 kg (11 lbs)
Afmetingen (B x L x H)	705 x 707,8 x 316,5 mm
Lichtsluiter	Standard
Verzegelde DLPTM-kern	Standard
ScenergiX	Standard horizontal and vertical electronic edge blending
Naadloos schakelen	Standard (wipes, fades, ...)
Picture-in-Picture	Up to 4 sources simultaneously (2 data, 1 video and 1 SDI)
Digitale zoom	Standard
Lens-encoders	On zoom and focus (with TLD lenses)
Gekoppelde Constant Light Output	not available
Compatibiliteit invoerbron	1600 x 1200 (max. input)
Vaste ingangen	<ul style="list-style-type: none"><li>■ 1x configurable 5 cable (BNC)</li><li>■ 1x composite Video (BNC)</li><li>■ 1x S-Video (4-pin DIN)</li><li>■ 1x analogue RGB (D15 Connector)</li><li>■ 1x SDI/HDSDI ( + loop-through)</li><li>■ 1x DVI (Digital Visual Interface)</li></ul>
Modulaire ingangen	not available
Controle	· 1 x RS-232 / 422 IN · 1 x RS-232 / 422 OUT · 1 x XLR female (2 way) · build-in RF remote transceiver (optional)

**Product specificaties****RLM H5 PERFORMER**

Verschuivingsbereik	Lens	Shift Range
	RLD 0.8	up-down: 35<>35 left-right: 15<>15
	Other RLD	up-down: 130<>40 left-right: 50<>50
	TLD (HB) 0.8	up-down: 90<>50 left-right: 40<>40
	Other TLD (HB)	up-down: 140<>50 left-right: 50<>50
Projectieverhouding	Lens	Throw ratio
	RLD 0.8	0.64
	RLD 1.5 - 1.8	1.2 - 1.44
	RLD 1.8 - 2.25	1.44 - 1.8
	RLD 2.25 - 3.0	1.8 - 2.4
	RLD 3.0 - 4.5	2.4 - 3.6
	RLD 4.5 - 7.0	3.6 - 5.6
	TLD (HB) 0.8	0.8
	TLD (HB) 1.6 - 2.0	1.6 - 2.0
	TLD (HB) 2.0 - 2.8	2.0 - 2.8
	TLD (HB) 2.8 - 5.0	2.8 - 5.0
	TLD (HB) 5.0 - 8.0	5.0 - 8.0
Bestelgegevens	R9010300	

Laatst bijgewerkt: 15 Mar 2023

© 2018 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Vanwege voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Raadpleeg [www.barco.com](http://www.barco.com) voor de meest recente specificaties.