

# SP4K-55

52,000 lumens smart cinema projector



- **Brilliant image**
- **Ready for tomorrow, today**
- **Barco EcoPure<sup>TM</sup>**
- **Fit and forget**

SP4K-55 is part of the Series 4 portfolio, designed in close collaboration with industry partners. Market trends in content creation, exhibition and technology were taken into account. The result? A next-generation laser projection family for all cinema screens. The SP4K models come in many different configurations offering you the freedom of choice. A wide range of brightness options, compatibility with both Barco lenses and selected 3rd party lenses, as well as a touch display and live streaming option. Play with the available options to match your specific needs.

### Brilliant image

The SP4K models of the Series 4 family brings native 4K resolution, higher contrast and enhanced uniformity into the movie theater. The Barco Active Image Management<sup>TM</sup> includes patented technology to guarantee sharp, consistent image quality over time.

### Ready for tomorrow, today

With the SP4K models and their RGB laser lightsource, the Barco Colorgenic<sup>TM</sup> technology opens up more than 98.5% of Rec. 2020. Moreover, all SP4K models are fully enabled for future innovations like 4K 120fps and compatibility with the latest immersive audio standard.

### Fit and forget

The modular design of the Series 4 projectors allows for cost-effective maintenance. There are only six Barco laser plate<sup>TM</sup> spare parts to service all light source configurations. Anyone can replace the filters thanks to the toolless cover and filter handling. The SP4K-55 seamlessly integrates into your current setup.

## Product specifications

## SP4K-55

### General specifications

Native brightness	52,000 lumens (typical)
Native contrast ratio	2000:1 (typical) up to 3000:1 with HC lens
Digital MicroMirror Device™	3x 1.38" DC4K
Resolution	native 4K: 4096 x 2160
Color gamut	DCI P3 compliant (100% of Rec.2020; when measured in xy-color coordinates)
Light source	Laser
Prime lenses	0.8; 1.01; 1.13-1.72; 1.35-1.86; 1.46-2.10; 1.65-2.60; 2.00-3.35; 2.53-4.98 High-brightness and high-contrast B-lenses compatible
Long-term brightness stability	40,000 hrs @ average usage conditions
Housing	integrated and external cooling design and patented sealed optical assembly
Dimensions (WxLxH)	projector incl. feet 760 x 1470 x 612 mm 29,92 x 57,54 x 24,09 inches external cooler: 546 x 462 x 589 mm 21,50 x 18,19 x 23,19 inches
Weight	projector incl. feet: 175kg/385lbs external cooler incl. feet: 31kg/68lbs
Power requirements	Single phase or triple phase 200-240V 25A Cooler: obtains power from the projector
Heat load (max. power)	14,500 BTU/hr
Exhaust airflow	Projector: 615CFM External cooler: 450CFM
Ambient temperature	40°C / 104F max.
Ambient humidity	85% RH max.
Media server	Barco Alchemy ICMP-X and other media server brands ** supported
Power consumption	4.2kW (3W in Eco mode)
Noise Level	Projector: 51dB(A) External cooler: 50dB(A) @1m and 25°C ambient temperature
3D systems	Active glasses systems and polarization systems on silver screens are supported. Color separation systems are not supported.
Safety requirements	Class 1 risk group 3
User interface	Touch Display and/or web based
Notes	Cooling liquid hose and cable length: 2.5m or 5m (8.2ft or 16.4ft) Vertical separation between cooler and projector: Maximum 3m (10ft) ** projector configuration with ICP-D; contact Barco service for the list of supported brands

Last updated: 09 Jul 2024

© 2024 Barco nv. Wszelkie prawa zastrzeżone. Powielanie w całości lub w części bez pisemnej zgody jest zabronione. Wszystkie nazwy marek i produktów są znakami towarowymi, zastrzeżonymi znakami towarowymi lub nazwami handlowymi odpowiednich właścicieli. Ze względu na ciągłe innowacje, informacje i specyfikacje techniczne mogą ulec zmianie bez wcześniejszego powiadomienia. Sprawdź [www.barco.com](http://www.barco.com), aby uzyskać najnowsze specyfikacje.