


SLM G8 Executive



技术规格

SLM G8 EXECUTIVE

一般规格

光输出	8000 ANSI lumens
数字微镜器件	three XGA DMDs (1024 x 768)
分辨率	1024 x 768 (native)
灯泡	2.0 kW Xenon illumination system Typical lifetime: 500 hours Max. lifetime: 1000 hours
对比度	> 500:1 (full white/full black) High Contrast Mode: > 1000:1
屏幕宽度	5m -15m / 6ft -50ft
兼容性	All video sources in Composite, S-VHS, Component or RGB formats or serial digital format All currently proposed HDTV, extended and improved television standards Most Macintosh computers Computers and electronic workstations with a resolution up to 1600 x 1200 pixels Two digital input slots allow direct digital interfacing with current and future digital inputs
镜头	Fixed focal length lenses are available with a throw ratio of 0.8:1 (very short throw ratio, specially designed for rear screen on-axis projection) or 1.2:1 (long throw). Motorized Zoom Lenses with a throw distance of 1.6-2.0,2.0-2.8,2.8-5.0,5.0-8.0 times the screen width
输入	2 x multifunctional 5-Cables input (high bandwidth) for the connection of: -RGB analog signals with standard sync (BNC) or tri-level sync, sync on green or separate sync -Standard video signals -S-VHS signals 2 x DVI in + 1 x DVI out SDI loop-through (Serial Digital Input) Video input
可选	SDI loop-through (Serial Digital Input) HD-SDI loop-through (High Definition Serial Digital Input) Network card
通信	1 x D9 connector for RS232 or RS422 loop-through 1 x D9 connector for peripherals 1 x 3-pin male XLR connector for wired remote network connection
特殊性能	Linked Constant Light Output balances the brightness of 'linked' SLM Executive projectors True Seamless Switching and cross-fade effects Click-and-Play  fast-swap lenses Built-in light shutter Optional edge-blending software ScenergiX
噪音级别	< 54 dBA
功率消耗	2550 W
电源	230 V (tolerance 180 V -255 V)
安全级别	Compliant with UL1950 and IEC950
电磁干扰	BARCO's SLM Executive Series complies with FCC rules & regulations, part 15 Class A and CE EN55022 Class A
净重	Net Weight: 45 kg / 99 lbs
网络连接	Optional
特性	· Picture-in-picture · Seamless source switching with effects
尺寸(宽x长x高)	529 x 795 x 429 mm (20.8 x 31.3 x 16.9 inch)
镜头移动	TLD Lenses Motorized V shift: -20% +118% Motorized H shift: max. 65% (L+R) For specific details per lens type: see lens product pages
ScenergiX	Standard
封装DLP™内核	Not available
无缝切换	Standard

生成于: 09 Jul 2024

© 2024 巴可公司。保留所有权利。未经书面许可，禁止全部或部分复制。所有品牌名称和产品名称均为其各自持有者的商标、注册商标或商号。由于不断创新，信息和技术规格如有变更，恕不另行通知。请查看www.barco.com.cn以了解最新规格。