

RDA-144

Re-configurable Distribution Amplifier



Общие характеристики	
Ввод видео	Number: Supports (4) high-bandwidth video inputs Video Type: RGBHV, RGBS, RGsB, RsGsBs, Component, S-Video, Composite Connectors: (5) BNC connectors per input channel Video Level: 1.0V p-p (nominal); 2.0V p-p (maximum) Sync Levels: Separate C or H/V, 0.7 to 5V p-p; Sync on Green: -0.3V Impedance: 75 ohms
Производительность усилителя распределения	Video Bandwidth: 450 MHz ; 375 MHz in fully bridged 1:16 configuration Gain: Unity
Выход видео	Number: Supports (16) high-bandwidth video outputs Video Type: RGBHV, RGBS, RGsB, RsGsBs, Component, S-Video, Composite Connectors: (5) BNC connectors per output channel Video Level: 1.0V p-p (nominal); 2.0V p-p maximum Sync Level: TTL sync, 0-3.5V levels Impedance: 75 ohms Re-configuration Options: ▪ (4) 1:4 distribution amplifiers ▪ (1) 1:8 and (2) 1:4 distribution amplifiers ▪ (2) 1:8 distribution amplifiers ▪ (1) 1:12 and (1) 1:4 distribution amplifiers ▪ (1) 1:16 distribution amplifier
Физический	Chassis: Rugged metal enclosure suitable for table top or rack-mounting Dimensions: 5.25" high x 17"wide x 13"deep ShippingWeight: 22 lbs. Agency Approvals: UL, CSA and CE
Входная мощность	110/220 VAC, 50/60 Hz, 75 W maximum
Относящийся к окружающей среде	Temperature: 0-40 degrees C Humidity: 0-95%, non-condensing
Гарантия	All video products are designed and tested to the highest quality standards and are backed by a full three-year parts and labor warranty.

Создано: 09 Jul 2024

© 2024 Барко нв. Все права защищены. Полное или частичное воспроизведение без письменного разрешения запрещено. Все названия брендов и продуктов являются товарными знаками, зарегистрированными товарными знаками или торговыми наименованиями соответствующих владельцев. В связи с непрерывными обновлениями информация и технические характеристики могут меняться без предварительного уведомления. Пожалуйста, проверьте www.barco.com для получения последних спецификаций.
www.barco.com

