


# ICX1.2-E

1.25mm pixel pitch, high-res indoor LED display, super-high cost-effective



- 27" tiles in 16:9 aspect ratio
- Unparalleled image quality presentation, 100% coverage of Rec. 709 gamut
- Easy to use, install and maintain
- Maximized product uptime

The new ICX series further expands Barco's indoor high-resolution LED tiles portfolio. The 27" inch tiles with a pixel-pitch ranging from 0.9mm to 1.8mm deliver superior seamless results, and the series includes all necessary features to maximize the reliability of your LED wall.

### Superior viewing experience

With each tile having a 16:9 aspect ratio, it is child's play to create native Full HD or UHD screens. This allows displaying video in the most common formats in full, without compression or unused canvas. What's more, the camera-supported seam correction technology makes sure tiles easily align, creating a single seamless canvas viewing experience.

### Easy to install and maintain


Because these LED tiles are designed for wall mounting, they are fully accessible from the front – creating a shallow depth. The improved robustness and the Assisted Module Extraction make sure the tiles can be easily removed, for maintenance or replacement needs, with a reduced risk of pixel damage.

### Consistently superior image quality

Barco-customizable light source is adopted to make the color reach Rec.709 standard. The screen is further improved in the color gamut, gray level and detail presentation. With all the core components of first-class quality, the screen has perfect flatness and wide viewing angle, and the professional visual image rendering in the future 7/24 use of the control room achieves the best effect.

### Unrivaled reliability

In order to support the use of Direct LED in critical environments and prevent



downtime, redundancy of both power and data can be integrated in the XT series. Also, instead of facing sudden complete wall downtime, the users can get a warning so proactive measures can be taken against potential wall failures.

### **Super-high cost-effective**

All components of ICX series products are made of high-quality materials, which ensures the long service life of the whole screen and ultra-high cost performance. What you see is what you get.

**Product specificaties****ICX1.2-E**

General specifications	
Pixelpitch	1.25 mm
Pixels per paneel	480 x 270 px H x V
Led-levensduur	100000 h video-50% brightness
Helderheid	600 nits
Pixeldichtheid	640000 (Pixels/ m <sup>2</sup> )
Verwerking	16 bits
Kleuren	281 trillion
Controle	Novastar
Kleurtemperatuur	2000K to 9500K adjustable
Vernieuwingsnelheid	3840 Hz
Hor. kijkhoek	155° +/-5°@50% brightness
Vert. kijkhoek	140° +/-5°@50% brightness
Helderheidsuniformiteit	>98%
Dimmen	0-100%
Contrast	∞5000:1
Energieverbruik	175W/m <sup>2</sup> typ. ∞ 460W/m <sup>2</sup> max.
Warmtedissipatie	584 BTU/h typ. ∞ 1534 BTU/h max.
Netspanning bij gebruik	100-240V / 50-60 Hz
Bedrijfstemperatuur	-20°C to +50°C
Operationele vochtigheid	10-95%
IP-classificatie	IP30
Afmetingen	600 x 337.5 x 25 mm W x H x D
Gewicht / tegel	4.5 kg
Onderhoudsgemak	Front service
Vervangen Module	magnet automatically adsorbs
Naadcompensatie	Automatic calibration compensation for camera
Certificeringen	CCC
Garantie	1 year

Laatst bijgewerkt: 12 Apr 2024

© 2018 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Vanwege voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Raadpleeg [www.barco.com](http://www.barco.com) voor de meest recente specificaties.