



OverView OL-710

Fully redundant 70" WXGA 16:9 LED video wall



Barco's OverView OL series LED-lit video walls are the first choice for 16:9 mission-critical control rooms that require a guaranteed uptime. The modules' high level of redundancy, not only of the individual LEDs, but also of the LEDs' power supplies and even inputs, ensures nothing can go wrong, giving users the peace of mind they need.

Furthermore, the OverView OL-710 video wall modules have been designed for an entirely maintenance-free operation over several years, without any need for consumables. Barco's unique liquid cooling system ensures lower LED temperature, resulting in longer LED lifetime (>80,000 hours in eco mode).

Always the most optimal picture

Displaying the sharpest and most saturated colors in WXGA resolution (1368x768), the OverView OL-710 offers an ergonomically excellent viewing experience. OverView OL series video walls also come with Sense⁶, Barco's unique sensor technology that provides brightness and color stability over time and across the entire display. Sense⁶ continuously measures brightness and color by means of a high-quality spectrometer, and adjusts the color space to provide an image that is most convenient for the human eye. The colors can also be adjusted to the very specific needs of TV cameras, making the OverView OL series suitable for backdrop applications.

Smarter design, without the gaps

The optional NoGap technology eliminates the gap traditionally found between the video wall cube screens. These gaps are necessary to compensate for changes in temperature and humidity. The special NoGap screens, however, are not subject to environmental conditions, so they can be placed immediately against one another. Additionally, the screens are incredibly robust, making them not only easy cleanable,

The optional NoGap technology eliminates the gap traditionally found between the video wall cube screens. These gaps are necessary to compensate for changes in temperature and humidity. The special NoGap screens, however, are not subject to environmental conditions, so they can be placed immediately against one another. Additionally, the screens are incredibly robust, making them not only easy cleanable, but also earthquake-proof. The individual modules also have the smallest depth on the market today, allowing to build the most shallow video walls possible. This makes the OverView OL series the product of choice for installation in confined spaces.

Highest level of redundancy

- 6x redundancy of LEDs (per color) & LED power supplies
- 2x redundancy of dual-link inputs

Unique Barco innovations

- Sense⁶ automatic full spectrum calibration
- Active liquid cooling

Excellent viewing ergonomics

- Wide LED color gamut
- WXGA resolution
- No color break up
- Excellent off-axis viewing with next-generation screen types

Maintenance-free

- 80,000 hours LED lifetime in eco mode
- 5 years service-free runtime
- No color wheel needed

Green focus

- No wearing parts, no waste
- No mercury lamps needed

Product specifications**OVERVIEW OL-710****General specifications**

Resolution	WXGA (1368x768 pixels)
Brightness	On-screen: 235 Cd/m ²
On-screen contrast	560,000:1
Color	Up to 165% EBU (at maximum color mode)
Display technology	Rear projection DLP
White point	3,200K 6,500K 9,300K arbitrary
Brightness uniformity	95% ANSI 9
Screen	FXS, with H/V 35°/33° (+/-2°) half gain angle
Screen gap	Hor: 1.0 mm 0.04", Vert. 0.7 mm 0.03" (@ 25°C) Hor: < 0.4 mm 0.015", Vert. < 0.3 mm 0.012" (@ 30°C)
Screen gap with optional NoGap screen technology	Hor: 0.1 mm 0.004" Vert. 0.1 mm 0.004" All temperature/humidity conditions
Color stability	Self calibration with spectrometer based Sense ⁶
Dimensions	<ul style="list-style-type: none">• Diagonal: 70" (Approx.)• Width: 1,550 mm 61"• Height: 872 mm 34.3"• Depth: 622 mm 24.5"• Weight: Projection Module: < 63 kg 139 lbs• Weight: Pedestal: < 39 kg 86 lbs
Light source	6x redundancy for each of 3 LED's
Light source lifetime	> 60,000h (at 6500k) > 80,000h in eco mode MTBF LED > 500,000 h
Conditions for operation	10°C-40°C, 50°F-104°F, 80% humidity (non-condensing)
AC input voltage	90 – 240 V, 50-60Hz
Power	170W (eco) 230W (typ.) 350W (max)
Heat dissipation	580 BTU/h (eco) 785 BTU/h (typ.) 1,194 BTU/h (max)
Signal	2x Dual link DVI-D in / 2x Dual link DVI-D out Single link DVI-D in, with HDCP (optional)
Direct ethernet access	Built in web server
Graphical user interface	All settings and operational parameters
Pixel clock	330 MHz
Input frequency	24 – 62 Hz
Genlock	49 – 61 Hz
Signal processing	Loop through Free cropping, free scaling (optional)
Integration to third party equipment	WEB service API (optional)
Warranty	2 years

Last updated: 08 Jul 2024

© 2024 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check www.barco.com for the latest specifications.