

OverView mL50

50" Display Wall system integrating TFT-LCD technology.



Product specificaties

OVERVIEW ML50

General specifications

Wisselstroom	95-230 VAC $\pm$ 10%, 50-60 Hz
Helderheidsuniformiteit	> 85 %
Compatibiliteit	BARCO's Display Walls integrate with the existing network environment and video sources via BARCO's controlware through a PanelLink™ interface
Contrast	250:1
Diepte	1215 mm / 47.83 "
Naleving van milieuwetgeving	ambient temperature 10-35°C 50-100°F humidity max. 80% (non condensing)
Hoogte	750 mm / 29.53 "
Ingangsfrequenties	mains frequency 50 ... 60 Hz
Lamp	200 W metal halide short-arc lamp, integrated in a pre-adjusted lamp module, no re-adjustment after replacement operation time typ. 5,000 hours
Lcd-panelen	Single-LCD TFT
Luminantie	typ. 90 cd/m ² or 200 lumens
Energieverbruik	260 W
Resolutie	resolution per cube : VGA: 640x480 color pixels XGA: 1024x768 color pixels
Veiligheidsvoorschriften	• vibrations tested according to IEC 68-3-3, IEC 68-2-2, JEAG 3605
Schermafmaat	50" diagonal
Gewicht	darkbox 36 kg / 79.36 lbs illumination unit 13 kg / 28.66 lbs screen module 16 kg / 35.23 lbs total module 65 kg / 143.3 lbs, distributed over 6 adjustable feet
Breedte	1,000 mm / 39.37 "

Laatst bijgewerkt: 09 Jul 2024

© 2024 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Als gevolg van voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Controleer www.barco.com voor de nieuwste specificaties.

www.barco.com

BARCO