

Helix™ G75

Flexible LED curtain display



IP66
WATERPROOF



Product specifications**HELIX™ G75****General specifications**

Pixel pitch	75 mm
Color	48-bit color per pixel
Packaging	Clear housing/black wires
Weather rating	IP66
Pixels per tile	4x32
Max. power consumption	50W
Mains Voltage	24 VDC
Brightness	444 nits
Dimensions	Width: 300 mm (11.8 in.) Height: 2,400 mm (94.5 in.) Depth: 14 mm (0.6 in.)
Area	0.72 m2 / G75 Grid Extensible to any width and 8 high
Viewing angle	120° x 120° (50% brightness)
Pixel configuration	RGB 3-in-1 LED
Compliance	ETL, FCC, CE, RoHS (pending)
Lifetime	>100,000 hours at full white to 50% brightness

Last updated: 10 Jul 2024

© 2024 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check www.barco.com for the latest specifications.