


# AC-ARS5

High-reach wall arm



The AC-ARS5 high-reach wall arm is designed for use with the Barco Smart Terminals with standard VESA mounting holes. The arm has a wide reach and offers great flexibility and compatibility for installation at the bedside in a typical hospital room.

### **Easy to install and operate**

This arm features an advanced locking system for easy, one-man installation and a standard VESA mounting for maximum compatibility. A smart tilt mechanism ensures the arm is easily maneuverable, providing the user with the most comfortable position when using the touchscreen of the terminal.

### **A perfect fit for the hospital room**

The AC-ARS5 is fully covered, making it easy to clean and disinfect to ensure patient safety at all times. The slim, stylish design and long reach make it ideal for installation in modern hospital rooms.

## Product specifications

## AC-ARSS

### General specifications

Body material	Aluminum and steel
Color	Barco White
Length	1,914 mm first section: 996 mm second section: 917 mm
Reach	1,914 mm
Height	Height adjustable +25° to -55° from horizontal, total 950 mm up (+25°): 324 mm, down (-55°): 626 mm
Rotation	Middle hinge: 330° VESA arm head hinge: 330° Integrated rotation stops inside the casting joints
Tilt	From horizontal: up: 60° down: -60°
Articulation forces allowed	Less than 30 N
Movement	Ease of movement in all articulations
Carrying capacity	4.0 kg -7.5 kg (adjustable)
Arm weight	9 kg
Cover	Casing with plastic covers can be cleaned to medical standards
Mounting	Compatible with standard VESA 75x75mm and 100x100mm Arm head cover perfectly matches with Barco terminals
Cable management	All cabling is internal to the arm DC Power, 1x Ethernet, 1x Service Call, 1x USB (USB cables support USB peripherals offered by Barco. To ensure correct operation, customers are to contact Barco with any specific requirements for external USB devices they would like to use, whereby a sample may be required to be sent to Barco for testing.)
Other	Arm head hinge allows for terminal 'tilt' function, with +/-50° up/down range from vertical Unique arm head allows for perfect (+/-5°) horizontal adjustment of the terminal Locking mechanism allows for installation by down to a single qualified person Grounding performed via electrical connection through the arm body Compatible with Barco wall boxes

Last updated: 04 Jul 2024

© 2024 Barco nv. Wszelkie prawa zastrzeżone. Powielanie w całości lub w części bez pisemnej zgody jest zabronione. Wszystkie nazwy marek i produktów są znakami towarowymi, zastrzeżonymi znakami towarowymi lub nazwami handlowymi odpowiednich właścicieli. Ze względu na ciągłe innowacje, informacje i specyfikacje techniczne mogą ulec zmianie bez wcześniejszego powiadomienia. Sprawdź [www.barco.com](http://www.barco.com), aby uzyskać najnowsze specyfikacje.