

# Consul

Compact, Dual Screen, L-Shaped Projection Table



- Super-flexible IR emitter holders enable orientation of the emitters optimal reception of the IR synchronization signal.
- Dedicated space for storage of VR accessories such as active glasses.
- Pop-up shelf for support of VR peripherals and accessories.

**Product specifications****CONSUL****General specifications**

Compatibility	Compatible with all sources from Video up to 1600 x 1200 pixel resolution workstations
Optional	Standard green phosphor tube for non-stereoscopic projection Built-in electromagnetic protected loudspeakers
Scan Frequencies	Horizontal: 15 -110 kHz autolock Vertical: 37 -200 Hz autolock
Screen size	Size: 2x 67"(2 x 1,7 m) diagonal DAB(Diffuse and Bright) screen

Last updated: 09 Jul 2024

© 2024 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check [www.barco.com](http://www.barco.com) for the latest specifications.