

DP-1200

2K Digital cinema projector for screens up to 12m (40ft)



Product specificaties**DP-1200****General specifications**

Digital MicroMirror Device™	3 x 0.98" DC2K dark metal devices
Native resolutie	2048 x 1080
Behuizing	Hermetically sealed DMD™ and optical assembly
Lamp	1.2kW -2kW Xenon lamp size
Schermbreedte	Screen width (screen gain 1:2) @ 14ft* : up to 12m -40ft (*): $\pm 10\%$ variation possible between units
Contrastverhouding	2000:1
Digitale video-ingangen	2 x SMPTE 292M inputs 2 x DVI input both selectable as single or as dual link
Primelenzen	1.2-1.8 1.4-2.05 1.6-2.5 1.95-3.2 2.4-3.9
Projectordiagnose	via PC touch panel via Communicator control software via SNMP agent
Voedingsvereisten	200-240 VAC, 50-60 Hz, 15 amps at 200 VAC
Afmetingen	projector: 505(H) x 689(W) x 1018(D) mm 19.9(H) x 27.1(W) x 40.0(D) inch NB: min. 5 cm of air inlet spacing required at the bottom of projector
Gewicht	projector: 93kg (205lbs)
Omgevingstemperatuur	max. 35°C / 95°F
Opties	CLO-constant light output ACS-2048 SNMP agent
Montage	universal pedestal (optional)

Laatst bijgewerkt: 09 Jul 2024

© 2024 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Als gevolg van voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Controleer www.barco.com voor de nieuwste specificaties.