

Magik II

Universal VGA interface



기술 사양

MAGIK II

일반 사양	
입력	• RGB analog on 5 BNC • Signal levels: R, G, B: 0.7 Vpp (no sync) or 1 Vpp with sync @ 75 Ohm • Sync: TTL @ 22 K load/analog
출력	• RGB analog on 5 BNC connectors (to projector or monitor): R, G, B: 0.7 Vpp (no sync) or 1 Vpp with sync @ 75 Ohm • RGB analog loop through on D15 connector (local monitor out): R, G, B: 0.7 Vpp (no sync) or 1 Vpp with sync 75 Ohm • Gain fixed to 1 • Two LEDs indicate signal presence on the BNC sync output (H)
RGB 대역폭	300 MHz @ -3dB
호환성	All desktop or portable computers with resolutions from VGA up to QXGA (2,048 x 1,532)
표준 액세서리	Included: • Bracket and set of wing screws for easy mounting underneath a table or any other enclosure • Two power cords for both US and European power outlets
AC 전원	Auto ranging power supply 87 -240 V AC 50/60 Hz
안전 규정	Compliant with UL1950 and EN60950
전자파 장애	Barco's Magik II complies with FCC rules & regulations, part 15 Class B and CE EN55022 Class B
크기	width x height x depth 218 x 45 x 150 mm 5.58 x 1.77 x 6.30 inch
무게	1.20 kg / 2.64 lbs.
옵션	19" rack mount (order n° R9828970)

작성일: 09 Jul 2024

© 2024 Barco nv. All rights reserved. 서면 허가 없이 전체 또는 부분을 복제하는 것은 금지됩니다. 모든 브랜드명 및 제품명은 상표, 등록 상표 또는 해당 소유자의 상표입니다. 지속적인 혁신으로 인해 정보 및 기술 사양은 사전 고지 없이 변경될 수 있습니다. 최신 사양은 www.barco.com을(를) 확인하세요.

