



# IBX1.2

1.25 mm pixel pitch, high-res indoor LED display, highly cost-effective



- **27" tiles in 16:9 aspect ratio**
- **Unparalleled image quality presentation**
- **Lower power consumption**
- **Maximized product uptime**

The new IBX series further expands Barco's indoor high-resolution LED tiles portfolio. The 27" inch tiles with a pixel-pitch ranging from 1.2 mm to 1.8 mm deliver superior seamless results, and the series includes all necessary features to maximize the reliability of your LED wall.

### **Superior viewing experience**

With each tile having a 16:9 aspect ratio, it is easy to create native Full HD or UHD screens. This allows displaying video in the most common formats in full, without compression or unused canvas. Because these LED tiles are designed for wall mounting, they are fully accessible from the front – creating a shallow depth.

The screen is improved for optimal color gamut, gray level and detail presentation, and was designed to have perfect flatness and wide viewing angle. The IBX series also offers optional remote monitoring, control & automatic calibration features, making sure the entire wall is perfectly uniform at any time.

### **Super-high cost-effective**

With a lower power consumption compared to competing models, the IBX series make sure you don't waste your budget on your electrical bill. Furthermore, all components of IBX series products are made of high-quality materials, which ensures the long service life of the whole screen and ultra-high cost performance. What you see is what you get.

**Product specificaties****IBX1.2**

General specifications	
Pixelpitch	1.25 mm
Pixels per paneel	480 x 270 px (H x V)
Helderheid	600 nits
Led-levensduur	100,000 hours (to 50% brightness)
Pixel dichtheid	640000 (Pixels/ m2)
Vernieuwingsnelheid	3840 Hz
Interne verwerking	16 bits
Hor. kijkhoek	160° (@50% brightness)
Vert. kijkhoek	160° (@50% brightness)
Helderheidsuniformiteit	>97%
Contrast	8000:1
Energieverbruik	200 W/m <sup>2</sup> (typ.) 600 W/m <sup>2</sup> (max.)
Warmte dissipatie	682 BTU/h/ft <sup>2</sup> (typ.) 2046 BTU/h/ft <sup>2</sup> (max.)
Netspanning bij gebruik	90 VAC -264VAC, 50-60 Hz
Redundante voeding	Yes (optional)
Bedrijfstemperatuur	-20°C to +50°C
Operationele vochtigheid	10 -85%
IP-classificatie	IP20
Afmetingen	600 x 337.5 x 25 mm (W x H x D)
Gewicht / tegel	7.5 kg (single PSU) 8 kg (dual PSU)
Materiaal	Cabinet: Die Cast Aluminium
Installatie	Front / Back access
Onderhoudsgemak	Front service
Certificeringen	BIS

Laatst bijgewerkt: 12 Apr 2024

© 2018 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Vanwege voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Raadpleeg [www.barco.com](http://www.barco.com) voor de meest recente specificaties.