

i70 Series

The intelligent, stand-alone visualization solution



Product specifications

170 SERIES

General specifications

Screen size	per channel : 68 inch diagonal screen with 4:3 aspect ratio. Black tinted high contrast screen offering a wide viewing angle
Lamp lifetime (typical)	6000 Hrs (Qx210L) -3000 Hrs (Qx350)
Inputs	<ul style="list-style-type: none">■ 1x Configurable 5-Wire (BNC) for composite video, S-video, component video, RGBHV, RGBS, RGsB■ 1x Composite video (BNC) (up to 7 composite video sources when using all connectors on top input board)■ 1x S-Video (4-pin mini-DIN; up to 3 S-video sources with BNC's)■ 1x VGA (D15 connector)■ 1x DVI (Digital Visual Interface) for sources up to SXGA+■ Audio: 3,5 mm jacks for microphone in, line in and line out■ RS232 in/out (D9 connector)(i70 Q Pro: LAN communication)
Networking	iQ Pro Server Specifications: <ul style="list-style-type: none">■ Processing Power: Pentium III socket with 1,2 Gigahertz Tualatin Celeron processor■ Memory: 256 MB RAM■ Storage: 40 GB hard disk■ Microsoft™ XP Multilanguage OS■ Inputs and outputs :<ul style="list-style-type: none">- PCMCIA slot for Wireless LAN cards, memory cards, Bluetooth, input extensions ...- RJ45connector for Ethernet (10Mb/s) and Fast Ethernet (100Mb/s)- 4 USB connectors
AC power	90 -254 VAC / 50-60 Hz
Power consumption	per channel : 380 Watts (Qx210L) -550 Watts (Qx350)
Heat dissipation	max 1810 BTU/Hr
Weight	per channel : 200 kg / 441 lbs

Last updated: 09 Jul 2024

© 2024 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check www.barco.com for the latest specifications.