

LC40-E



Product specifications**LC40-E****General specifications**

Technology	TFT LCD
Native resolution	1280 x 768 (W-XGA)
Active screen diagonal	1010mm (39.6")
Active screen area	862mm x 517mm (33.9" x 20.4")
Hor. viewing angle	170°
Vert. viewing angle	170°
Lifetime	typical 50.000h
Weight	25kg / 55.1lbs
Contrast ratio	600:1
Brightness	450NIT
Colors	16.8 million
Aspect ratio	15:9
Standard inputs	DVI, RGBHV (on BNC), SDI Video PAL/NTSC/SECAM (CVBS in/out; S-Video in; YUV in)
Control	RS232 control On Screen Display (OSD) IR Remote control
Power requirements	Input: 85V-264V (50Hz-60Hz)
Power consumption	270W (330W including Compact PC)
Operating T°	5°C to 40°C (41°F to 104°F)
Humidity	Max. 85%
Regulation Compliance	UL, CE

Last updated: 09 Jul 2024

© 2024 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check www.barco.com for the latest specifications.