

IO Gateway

AVoIP transcoder using IPMX/2110 open standards



- **Less equipment and maintenance**
- **Interoperability and flexibility thanks to standards-based workflows**
- **High quality at low latency**

Barco IO-H1 & Barco IO-H25

The Barco IO transcoders are the base of a simplified future-proof AVoIP setup transporting your current HDMI™ signals (up to 4K60 4:4:4) into an open standards based system with the lowest latency.

Reduce the need for additional switchers, cables, converters, etc. and just add the IO solution to convert and route from a single bi-directional cable solution containing multiple AV signals and control. It minimizes clutter and costs.

The Barco IO encoder/decoder is a network-based system which can accommodate a very large number of devices and operates on open standards making A/V integration much more accessible, more flexible and easier to maintain.

Each Barco IO-H1 package includes:

- IO-H1 1GbE over Cat5 encoder/decoder
- JPegXS
- Power supply
- Quick Mount™ Plate
- Mounting Bracket

Each Barco IO-H25 package includes:

- IO-H25 10/25GbE over Fiber
- JPegXS
- Power supply



- Quick Mount™ Plate
- Mounting Bracket

Barco IO-S25

The Barco IO transcoders are the base of a simplified future-proof AVoIP setup transporting your current 12G SDI signals (up to 4K60 4:2:2) into an open standards based system with the lowest latency.

Reduce the need for additional switchers, cables, converters, etc. and just add the IO solution to convert and route from a single bi-directional cable solution containing multiple AV signals and control. It minimizes clutter and costs.

The Barco IO encoder/decoder is a network-based system which can accommodate a very large number of devices and operates on open standards making A/V integration much more accessible, more flexible and easier to maintain.

Each Barco IO-S25 package includes:

- IO-S25 10/25GbE over Fiber
- JPegXS
- Power supply
- Quick Mount™ Plate
- Mounting Bracket

Algemene specificaties

Opmerkingen

The specifications in this document are preliminary

IO-H1

- Media Bandwidth: 1 or 2.5 GbE
- Media Connector: 1 x RJ45 (copper)
- Media Networks: 1 x main, 1 x redundant
- Control Network: 1 x 1GbE Copper
- Video Inputs: 1 x HDMITM 1.4, HDMITM 2.0
- Video Outputs: 1 x HDMITM 1.4, HDMITM 2.0
- Power: PoE+, external PSU
- IPMX Profile: Profile 3, 18:1 Compression

IO-H25

- Media Bandwidth: 10 or 25 GbE
- Media Connector: 1 x SFP+ (fiber)
- Media Networks: 1 x main, 1 x redundant
- Control Network: 1 x 1GbE Copper
- Video Inputs: 1 x HDMITM 1.4, HDMITM 2.0
- Video Outputs: 1 x HDMITM 1.4, HDMITM 2.0
- Power: PoE+, external PSU
- IPMX Profile: Profile 1 (Uncompressed), Profile 2 (4:1 compression)

IO-S25

- Media Bandwidth: 10 or 25 GbE
 - Media Connector: 2 x SFP+ (fiber)
 - Media Networks: 1 x main, 1 x redundant
 - Control Network: 1 x 1GbE Copper
 - Video Inputs: 1 x 12G-SDI
 - Video Outputs: 1 x 12G-SDI
 - Power: PoE+, external PSU
 - IPMX Profile: Profile 1 (Uncompressed), Profile 2 (4:1 compression)
-

Laatst bijgewerkt: 13 Mar 2025

© 2025 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Als gevolg van voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Controleer www.barco.com voor de nieuwste specificaties.