

Barco Helios Studio Edition



The Barco Helios is one of the most compact 3-chip DLP projectors available and features hand-selected optical components and matched lamps.

Helios is built to your order in our high-tech facility in Norway from the highest grade components available. An aluminum body, magnesium optical engine casing and 5 all glass lens options with a tolerance so extreme that only the top 5% produced are selected.

The Barco Helios Studio Edition challenges design conventions and pushes the boundaries of conceivable image quality.

技术规格

BARCO HELIOS STUDIO EDITION

一般规格

投影机类型	three chip, 0.95" 1080p DC4 DMD™
分辨率	1920x1080
光输出	up to 8500 lumens full power
对比度	>10000:1 (native optical contrast)
透镜范围	0.74:1, 1.2 – 1.70:1, 1.70 – 2.55, 2.5 – 4.00, 3.90 – 6.24:1
光学镜片移动	adjustable: vertical and horizontal, depending on lenses
灯	2x 400W FusionPlus VID1 UHP™
灯泡寿命 (典型)	Up to 1,500 hours (full power) / Up to 2,000 hours (eco mode)
可带灯运输	yes
封装DLP™内核	standard
兼容性	"1080i/p, 720p, 576i/p, 480i/p, PAL SECAM, NTSC digital and analogue RGB"
3D	"active eyewear (optional), 2x helios SE(stacked): INFITEC EX® 3D and Active Stereo IR, RF models"
输入	"1 x HDMI 1.4, 1 x YPbPr, 1 x S-video, 1 x Composite 2 x DVI-D, 2 x VGA, 1 x 5-BNC"
控制	"1 x RJ-45 TCP/IP, 1 x 9-pin D-SUB RS232, 1 x USB, 2 x 12V programmable trigger (3.5mm mini jack) IR remote control with IR repeater input AMX Device Discovery, Crestron Certified Partner"
电源	6.5A, 200-240V, 50-60Hz
功率消耗	880 W
工作温度	10 -40 °C
操作湿度 无冷凝	20 -80% RH
消散 BTU	
安装	table top, ceiling mount, straight down or up.
尺寸(宽x长x高)	501 x 604 x 250 mm(excluding lens)
净重	about 22 kg / 48.5 lbs. (excluding lens), shipping weight: 32 kg
装运尺寸	820 x 720 x 420 mm
机箱颜色	black and white
认证	CE, FCC Class A, UL and cUL
保修期	"3 years limited warranty, (optional extended 2 years) 90 days/500 hours on lamp. Conditions apply"

生成于: 09 Jul 2024

© 2024 巴可公司。保留所有权利。未经书面许可, 禁止全部或部分复制。所有品牌名称和产品名称均为其各自持有者的商标、注册商标或商号。由于不断创新, 信息和技术规格如有变更, 恕不另行通知。请查看www.barco.com.cn以了解最新规格。