

Retrodata 708 50"



Product specifications**RETRODATA 708 50"**

General specifications

Compatibility	Horizontal autolock scan frequency of 15-69 kHz Vertical scan frequency of 37-210 Hz RGB bandwidth of 75 MHz A wide range of PC graphics boards with a resolution up to 1280 x 1024 pixels/60 Hz Universal input signal connection facilities
Light output	2000 Nit/582 ftL. 176 Nit/52 ftL. (Economy mode) 234 Nit/69 ftL. (Normal mode) 277 Nit/81 ftL. (Boost mode)
Screen size	50"

Last updated: 08 Jul 2024

© 2024 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check www.barco.com for the latest specifications.