

固定式 OLite 612

<P>像素间距小、表面安装创意型 LED 显示单元</P>



12mm
PIXEL PITCH

IP65
WATERPROOF



技术规格

固定式 OLITE 612

一般规格

像素间距	12.4 毫米
亮度	6000 尼特
LED配置	3 合 1 SMD
像素密度	3,888 LEDs per tile (72x54) (rental) 1,944 LEDs tile (36x54) (fixed)
像素密度	3,888 LEDs per tile (72x54) (rental) 1,944 LEDs tile (36x54) (fixed)
水平观察角度	110° (至少 50% 亮度)
垂直视角	+40、-50° (至少 50% 亮度)
对比度	1150:1 (光强为 500 勒克斯)
寿命	50000 小时, 维持初始亮度的 50%
功率消耗	800 瓦/显示单元 (更大) -240 瓦 (平均) (租赁屏) 400 瓦/显示单元 (更大) -120 瓦 (平均) (固定式)
操作电压	200-240 伏/50-60 赫兹
瓦状尺寸	Width: 896mm (rental) Height: 672mm (rental) Depth: 246mm (rental) Width: 448mm (fixed) Height: 672mm (fixed) Depth: 116mm (fixed)
瓦状尺寸	Width: 896mm (rental) Height: 672mm (rental) Depth: 246mm (rental) Width: 448mm (fixed) Height: 672mm (fixed) Depth: 116mm (fixed)
瓦状尺寸	Width: 896mm (rental) Height: 672mm (rental) Depth: 246mm (rental) Width: 448mm (fixed) Height: 672mm (fixed) Depth: 116mm (fixed)
瓦状尺寸	Width: 896mm (rental) Height: 672mm (rental) Depth: 246mm (rental) Width: 448mm (fixed) Height: 672mm (fixed) Depth: 116mm (fixed)
重量 / 层数	58 公斤 (租赁) 17 公斤 (固定式)
IP等级	IP65/65
处理	16 位/色
颜色	28.1 兆
刷新率	800 赫兹
内置底座	更大高度 12 单元
内置构架	更大高度 15 单元
连接界面	DVI 接口 (DVI 接头)
更大导线长度	4.5 米 (带 Barco DVI 电线)
界面	2 个 DVI 链路
更大串联	3 个显示单元
可维护性	背面
工作温度	-20 -45°C
存储温度	-20 -60°C
工作湿度	10-99%
存储湿度	10-99%
信号源兼容性	CVBS、YC、YUV、RGB、DVI、SDI、HDSDI (DX700: 双链路 DVI、双链路 HDSDI)
可操作数字转换器	DX-700 (带 DVI 输出卡)、D320、LED-PRO
认证	UL/CE A类/TUV/FCC A类

生成于: 10 Jul 2024

© 2024 巴可公司。保留所有权利。未经书面许可, 禁止全部或部分复制。所有品牌名称和产品名称均为其各自持有者的商标、注册商标或商号。由于不断创新, 信息和技术规格如有变更, 恕不另行通知。请查看 www.barco.com.cn 以了解最新规格。