


FLM-HD20

20,000 lumens, 1080p HD, 3-chip DLP projector



Barco's FLM-HD20 is an ultra-bright, durable projector with full HD picture-in-picture capabilities. It is a perfect fit for any large venue that requires extra brightness to show clear, crisp images in a luminous environment.

Powerful projection for large venues

Thanks to the FLM-HD20's 20,000 lumens light output, it can display widescreen, high-contrast images of superior quality even in venues with lots of ambient light. Through its superior video processing and picture-in-picture capabilities, you can make your presentations more interactive and energizing without the need for extra peripherals.

Most silent projector in its class

The FLM-HD20's liquid cooling technology cuts noise levels to a minimum, making it one of the most silent projectors in its class. The FLM is also equipped with a sealed optical engine that prevents dust, smoke or other environmental contamination from affecting its image quality.

Ultra-bright and stunning images

- High contrast 3-chip DLP™ engine
- True native HD resolution
- 20,000 center lumens
- Contrast ratio of 1,800:1

Low total cost of ownership

- Sealed engine with constant image quality over time
- Projector designed for high resistance against external contamination

- Extended lamp warranty (750 hours)
- Extremely good lamp maintenance (typical 1,000 hrs)
- TLD+HD lens range that is fully compatible with the Barco's HDX projector series

Built for demanding rental & staging applications

- Fully sealed optics
- Easy to set up, install, service and transport
- Removable lamp house, power supply & electronics
- Low video delay (broadcast live events)
- Universal lamp house for all FLM projectors

Fit for any widescreen & creative application

- High brightness projection at 20,000 center lumens
- "High-Contrast Mode" (2,400:1) feature enables you to make a trade-off between brightness and contrast, depending on your application.
- Low video delay, very important when broadcasting live events
- Ultimate solution for projection on multiple screens and special surfaces

Projector Toolset software

The FLM comes with standard "Projector Toolset" software, offering basic control, diagnostics and other features (e.g. a lens program). Additional software plug-ins can be offered as an option delivering added functionality for multi-screen applications, advanced settings control, etc. A user friendly GUI (Graphical User Interface) ensures easy control.

Product specifications**FLM-HD20**

General specifications	
Projector type	Full HD 3-chip DLP digital projector
Technology	0.95" DMD™ x3
Resolution	1,920 x 1,080
Brightness	20,000 center lumens / 19,000 ANSI lumens
Contrast ratio	2,100:1 / 2,700:1 (high contrast mode)
Brightness uniformity	90%
Aspect ratio	16:9
ScenergiX	Horizontal and vertical edge blending
Lens type	TLD+
Lenses	0.73:1 ; 1.2:1 ; 1.25-1.6:1 ; 1.5-2.0:1 ; 2.0-2.8:1 ; 2.8-4.5:1 ; 4.5-7.5:1 ; 7.5-11.5:1
Optical lens shift	Vertical: -10% to +110% ; Horizontal: -50% to +50% (on zoom lenses)
Color correction	P7
Lamps	3kW xenon
Lamp lifetime	1,000 hours
Transport with lamp	Yes
Lamp house, quick replace	Yes
Customer bulb replace	Yes
Lamp warranty (field replace/ factory replace)	90 days, 500 hours / pro rata 750 hours
Sealed DLP™ core	Standard
Optical dowser	Standard
Picture-in-picture	Two sources simultaneously
Orientation	table -ceiling -side (portrait) -vertical
DMX 512	Optional
WARP	Preset values + custom
Integrated web server	N/A
CLO (constant light output)	Standard
3D ready (optional)	Passive Infitec

Product specifications**FLM-HD20**

Inputs	DVI(HDCP); 5-BNC RGBHV (RGBS/RGsB, YUV CS/SOY, Composite video, S-Video); SDI/HDSDI
Optional Inputs	DVI(HDCP); 5-BNC RGBHV (RGBS/RGsB, YUV CS/SOY, Composite video, S-Video); SDI/HDSDI
Input resolutions	From NTSC up to UXGA (1,600 x 1,200) incl. HD (1,920 x 1,080)
Max. pixel clock	165 MHz
Software tools	Projector Toolset
Control	XLR wired + IR, RS232
Network connection	10/100 base-T, RJ-45 connection
Power requirements	220-240V / 50-60Hz
Max. power consumption	3700W
Noise level (typical at 25°C/77°F)	58dB(A)
Operational ambient temperature	0-40°C / 32°-104°F
Operational humidity	0-80% (non condens)
Dissipation BTU	max 12,625 BTU/h
Dimensions (WxLxH)	707 x 1,025 x 548mm / 27.83 x 40.35 x 21.57 inches
Weight	99kg (218.25lbs)
Shipping Dimensions	(LxWxH) 1,200 x 980 x 760 mm / 47.24 x 38.58 x 29.92 inches
Shipping Weight from Factory	151kg (333lbs)
Standard accessories	Power cord, wireless/XLR wired rugged remote control
Certifications	Compliant with UL1950 and EN60950 complies with FCC rules & regulations, part 15 Class A and CE EN55022 Class A, RoHS
Warranty	2 years

Last updated: 15 Mar 2023

© 2018 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check www.barco.com for the latest specifications.