

SLM R12+ Performer

SXGA+, 12,000 lumens three-chip DLP projector



Product specificaties**SLM R12+ PERFORMER****General specifications**

Beeldscherm	Three-chip DLP (0.95" DMD x3)
Resolutie	1,400 x 1,050 pixels (SXGA+)
Lichtuitvoer	typically 12,000 ANSI lumens ($\pm 10\%$) typically 13,500 center lumens ($\pm 10\%$)
Contrastverhouding	1,600:1 (full field)
Helderheidsuniformiteit	90%
Beeldverhouding	4:3
ScenergiX	Horizontal and vertical edge blending
Lensverschuiving	Vertical: $x > -10\%$ to $+110\%$ Horizontal: $x > -50\%$ to $+50\%$ (small differences occur per lens type) (short throw lenses have less shift)
Type & sterkte van lamp	2.2kW xenon
Levensduur lamp (standaard)	1,000hrs
Kenmerken	Picture in picture (up to two sources on-screen simultaneously) P7 color processing (color matching)
Oriëntatie	Table/ceiling/side (portrait)/vertical
Invoer	Input SDI/HD-SDI/DVI 1x YUV1 (on RCA/cinch) 1x Composite video (on RCA/cinch) 1x S-Video (on 4-pin mini-DIN) Compatibility All current video sources (PAL, SECAM, NTSC) in Composite, S-VHS, Component or RGB formats All current HDTV sources All computer graphics formats from VGA, SVGA, XGA, SXGA, full HD to UXGA
Communicatiepoort	10/100 Mb/s Ethernet (on RJ45) -optional RS-232 IR external 2x 12V trigger
Netwerkverbinding	10/100 base -T Projector Toolset control
Wisselstroom	220 -240 VAC ($\pm 10\%$)/50-60 Hz
Energieverbruik	2,750 W
Geluidsniveau	Normal operation 62.5 dB
Afmetingen	492 x 876 x 585 mm
Gewicht	56 kg
Veiligheidsvoorschriften	Compliant with UL1950 and EN60950
Elektromagnetische storing	Complies with FCC rules & regulations, part 15 Class A and CE EN55022 Class A

Laatst bijgewerkt: 09 Jul 2024

© 2024 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Als gevolg van voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Controleer www.barco.com voor de nieuwste specificaties.